


1

Technical drawing of a mechanical part with dimensions:

- Overall width: 1.00 [25.4]
- Overall height: 1.00 [25.4]
- Internal width (from left face to start of internal feature): 0.63 [16.0]



FULL SCALE


PANDUIT PART NUMBER*	MAXIMUM CABLE DIA. in. (mm)	WEIGHT lbs. (g)/100pcs
LWC38-A	0.38 (9.6)	0.64 (292)

2) MOUNT IS DESIGNED TO SUPPORT
0.50 lbs (227g) MAX WEIGHT ON
A CLEAN DRY SMOOTH SURFACE.

-
- 0.56
[14.2]

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE, AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED, AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED, ARE BEYOND PANDUIT'S CONTROL.

DIMENSIONS IN BRACKETS ARE METRIC (mm)

							TITLE LWC38-A, LATCHING WIRE CLIP						
							CUSTOMER DRAWING						
							ITEM REVISION NAME 10B015KH/00						
							DATASET FILE NAME 10B015KH_DC/00 - GB0160BA_REV02						
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± 0.05 [1.3] .xxx ± 0.010 [0.25] .xx ± 0.02 [0.5] ANGLES ± 5 °					MATERIAL NYLON 6/6	
2	8/05/13	BWG	MPH	RTFI	REVISED MAX. CABLE DIA. AND REVISED NOTE 1	GB0160BA/02	 THIRD ANGLE PROJECTION					DRAWING NUMBER: GB0160BA	
2	8/05/13	BWG	MPH	RTFI	AND REVISED TITLE BORDER.	GB0160BA/02							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY JRL	DATE 11-11-93	CHK	SCALE 2X	SIZE A		

010100DA/16

2

1