



FEATURES:

- ✓ Converts BNC (female) cables / connectors to SMD test clips for test versatility.
- ✓ Grabber pincer and BNC center contact are gold plated for excellent corrosion resistance and low contact resistance to ensure test signal integrity.
- ✓ BNC connector is molded directly to the wire for pull strength durability and dust and moisture resistance.
- ✓ SMD clips attach to terminals up to .040" (1.0mm) diameter.
- ✓ Black wire is connected to BNC shell, red wire to BNC center contact.

MATERIALS:

BNC: Nickel Plated Brass, *Center Contact:* Gold Plated Brass

Dielectric: PTFE

Wire: 22 AWG, PVC Insulated

Grabber Pincer: Stainless Steel, *Gold Plated, Spring:* Stainless Steel

Insulation: Glass Filled Nylon, color matches color of wire

RATINGS:

Operating Voltage: Hands free testing in controlled voltage environments: 150 VRMS Max.

Operating Temperature: +131°F (+55°C) Max.

ORDERING INFORMATION: Model 5410*

* Custom lengths are available, contact Pomona Product Support at: 1-800-241-2060

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02"$ (.51 mm), .xxx = $\pm .005"$ (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies.

Sales: 800-490-2361 Fax: 888-403-3360 Technical Assistance: 800-241-2060
For "Where to Buy" information, visit the Pomona web site at www.pomonaelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Pomona:](#)

[5410](#)