

Quick Links

[RoHS/LF P/N Search](#)

Documentation

[Customer drawing search](#)

[Free search](#)


Services

[Distributor list](#)

Start > Search=55200204* > 55200204

55200204

55200204 : 2 way coupling Male housing



Customer drawing

ACTIVE



[Add to Favorites](#)

[Print Datasheet](#)

FCI Brings You More

[Contact our sales/technical support](#)

[Sample request](#)

Specifications

[Download document](#)

[Mating Half](#)

General **Mechanical** **Physical** **Terminal 1 Type** **Environmental** **Other Features**

General

Application	Wire to Wire Harness in-line
Ways	2
Coding version	C
Product Type	Housing
Coding	Yes
Features	Mechanical polarization Terminal position assurance (T.P.A.) Connector position assurance (C.P.A.) Rear sealing ensured by a pre-mounted grommet Fastening clip available
Hybrid	No
Main Terminal family	APEX
Main Terminal size	2.8 mm
Sealed	Yes
Terminal Size	2.8

Mechanical

Connector mating force	< 75N
-------------------------------	-------

Physical

Color	Dark Grey
Material	PA
Temperature (Range)	-40°C to +125°C

Terminal 1 Type

Terminal type 1	APEX Male 2.8 mm Terminal
Ways for Terminal Type 1	2
Contact insertion force for Terminal Type 1	< 15N
Contact Pitch for Terminal Type 1	5.25 mm
Retention force (Contact) for Terminal Type 1	> 90N

Environmental

IMDS	Yes
-------------	-----

Other Features

Market	Passenger Vehicles
Type	Male
Part Situation	Active

Disclaimer	The supply of some products might be limited to some customers For more information, please contact your local sales office. Displayed data is for information purposes only
-------------------	--