

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [39535-4519](#)
Status: **Active**
Description: 5.08mm Pitch Eurostyle™ Vertical PCB Header, with Threaded Retention Inserts, Surface Mount Compatible, Gold (Au) Plated, 19 Circuits

Documents:

[3D Model](#) [Product Specification PS-39500-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Terminal Blocks
Series [39535](#)
Application N/A
Component Type PCB Header
Product Name ESE, Eurostyle™Pluggable
Type Euro Block
UPC 822350495943

Physical

Circuits (Loaded) 19
Entry Angle N/A
Lock to Mating Part Yes
Number of Rows 1
Orientation Vertical
PC Tail Length 5.08mm
PCB Thickness - Recommended 3.20mm
Panel Mount No
Pitch - Mating Interface 5.08mm
Pitch - Termination Interface 5.08mm
Polarized to Mating Part Yes
Shrouded Closed Ends
Stackable No
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -40°C to +140°C
Wire Size AWG N/A


Electrical

Current - Maximum per Contact 15A
Voltage - Maximum 300V

Material Info

Reference - Drawing Numbers

Product Specification PS-39500-001
Sales Drawing SD-39501-002, SD-39535-001



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[39535Series](#)

Mates With

Most 5.08mm Pitch Industry Standard Plugs, [39534](#) Horizontal Plug with Retention Screws, [39537](#) Vertical Plug with Retention Screws

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

39535-4519