



- 1

MAXIMUM INSERTION LOSS IS 0.2 dB
PLUS CABLE ATTENUATION OF 1.5 dB/km
AT 1300nm. (SEE TABLE)
2. DIMENSIONS IN [] ARE IN INCHES.
3. PRODUCT AND PROCESSING MUST MEET
REQUIREMENTS OF TEC-138-702



0.20	3.50±0.05 [137.8±2.0]	9-6374659-3
0.28	50.00±0.50 [1968.50±19.68]	5-6374659-0
0.65	300.00±3.00 [11811.0±118.0]	9-6374659-9
0.35	100.00±1.00 [3937.0±39.0]	9-6374659-8
0.20	0.50±0.03 [19.68±1.18]	9-6374659-7
0.25	36.00±0.36 [1417.3±14.2]	9-6374659-2
0.24	27.00±0.30 [1063.0±12.0]	9-6374659-1
0.25	30.00±0.30 [1181.1±12.0]	3-6374659-0
0.24	25.00±0.30 [984.0±12.0]	2-6374659-5
0.23	20.00±0.30 [787.0±12.0]	2-6374659-0
0.22	15.00±0.15 [590.6±6.0]	1-6374659-5
0.22	12.00±0.15 [472.4±6.0]	1-6374659-2
0.21	10.00±0.15 [393.7±6.0]	1-6374659-0
0.21	8.00±0.15 [315.0±6.0]	6374659-8
0.31	76.2±0.76 [3000.0±30.0]	6374659-7
0.20	1.50±0.05 [59.5±2.0]	6374659-6
0.20	5.00±0.08 [196.9±3.0]	6374659-5
0.20	3.00±0.05 [118.1±2.0]	6374659-3
0.20	2.00±0.05 [78.7±2.0]	6374659-2
0.20	1.00±0.05 [39.4±2.0]	6374659-1
1 MAX IL (dB)	L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
C.S.VASU
22AUG05

CHK
J.DUNCAN
22AUG05

APVD
J.DUNCAN
22AUG05

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

CABLE ASSY, FIBER OPTIC, 62.5/125um LDD
ZIP, LC DUPLEX

SIZE
A2

CAGE CODE
00779

DRAWING NO
6374659

RESTRICTED TO

SCALE
NTS

SHEET
1 of 1

REV
E