

Spiral tube - WG-S HF 50 BK - 3241116

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Spiral hose, for easy bundling and guiding of cables and conductors, offers protection against slight mechanical strain

The figure shows a version of the article

Key commercial data

Packing unit	1 1
Minimum order quantity	25 1
Weight per Piece (excluding packing)	99.0 GRM
Custom tariff number	39269097
Country of origin	Poland

Technical data

Dimensions

Length (b)	25 m
Width (a)	50 mm

Ambient conditions

Ambient temperature (operation)	-50 °C ... 85 °C
Ambient temperature (assembly)	-20 °C ... 60 °C

General

Color	black
Type	Continuous strip
Inflammability class according to UL 94	HB
Components	free from silicone and halogen
Material	PE

Spiral tube - WG-S HF 50 BK - 3241116

Classifications

eCl@ss

eCl@ss 4.0	27140602
eCl@ss 4.1	27140602
eCl@ss 5.0	27140602
eCl@ss 5.1	27140602
eCl@ss 6.0	27400703
eCl@ss 7.0	27400703
eCl@ss 8.0	27400703

ETIM

ETIM 3.0	EC000012
ETIM 4.0	EC000046
ETIM 5.0	EC000046

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121411
UNSPSC 11	39121411
UNSPSC 12.01	39121708
UNSPSC 13.2	39121411

Accessories

Accessories

Cutting tools

Cutting tool - CUTFOX-ES - 1212621



Electrician's scissors, high cutting performance thanks to micro-serrated cutting area, suitable for copper, aluminum, Kevlar fibers, and plastic, two-component non-slip soft-grip handles, ergonomic design, adjustable screw joint