THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT INVENTORY NUMBERING SYSTEM



PANDUIT PART NUMBER	Min. Exp. I.D In. (mm)	Max. Rec. I.D In. (mm)	NOMINAL REC WALL THICKNESS In. (mm)
HSTTVA12	.125 (3.2)	.063 (1.6)	.021±.004 (.53±.102)
HSTTVA19	.187 (4.8)	.093 (2.4)	.023±.004 (.58±.102)
HSTTVA25	.250 (6.4)	.125 (3.2)	.029±.005 (.74±.127)
HSTTVA38	.375 (9.5)	.187 (4.8)	.029±.005 (.74±.127)
HSTTVA50	.500 (12.7)	.250 (6.4)	.030±.005 (.76±.127)
HSTTVA75	.750 (19.0)	.375 (9.5)	.035±.005 (.89±.127)
HSTTVA100	1.000 (25.4)	.500 (12.7)	.042±.007 (1.07±.178)
HSTTVA150	1.500 (38.1)	.750 (19.0)	.047±.008 (1.19±.203)

NOTES:

1. SHRINK RATIO: 2:1
2. SHRINK RATIOS ARE APPROXIMATIONS; PLEASE REFER TO TABLE 1 FOR THE EXACT MIMIMUM EXPANDED AND MAXIMUM RECOVERED I.D 'S.
3. MATERIAL: CROSSLINKED POLYOLEFIN WITH ADHESIVE
4. COLOR: BLACK
5. "ALL WARRANTIES, INCLUDING MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. (USER IS RESPONSIBLE TO DETERMINE SUITABILITY OF PRODUCT FOR INTENDED USE."

DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS: G00239K_PB_HSTTVA_00

PANDUIT CORP. TINLEY PARK, ILLINOIS

FLEXIBLE ADHESIVE LINED THIN WALL HEAT SHRINK (HSTTVA)

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 [1.3] (.XXX) ±0.010 [0.25]
(.XX) ±0.02 [0.5] ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES. THIRD ANGLE PROJECTION.

DRAWN BY: LGRAVITT

MAT'L: SEE NOTES

SCALE: NONE

DATE: 5/14/03

CHK'D:

DRAWING NO.: GB0239KN

SIZE: A

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP
R	5/14/03	LGG	[illegible]	INITIAL RELEASE	GB0239KN	R	