


MA 2,5/5.SNBTA


Spacing 5 mm (.200")



5 mm block - Switch connection by short blade - Equipped with two test sockets DIA. 2,3 mm / .090"

M 4/6.SNBT...


Spacing 6 mm + 0,05 (.238")



6 mm block - Switch connection by short blade - Equipped with two test sockets DIA. 2 mm / .079"

M 4/6.SNB

Spacing 6 mm + 0,05 (.238")



6 mm block - Switch connection by long blade

| Color | Type | Part numbers |
|-------------|----------------|--------------|
| Grey / Grey | MA 2,5/5.SNBTA | 0115 505.16 |

| Color | Type | Part numbers |
|-----------------|-------------|--------------|
| Grey / Grey | M 4/6.SNBT1 | 0115 438.12 |
| Grey / Beige V0 | M 4/6.SNBT2 | 0115 441.15 |

| Color | Type | Part numbers |
|----------------|--------------|--------------|
| Grey / Grey | M 4/6.SNB | 0115 686.13 |
| Orange/Orange | M 4/6.SNB | 0105 053.22 |
| Beige V0/Beige | M 4/6.SNB.V0 | 0195 686.14 |

| Characteristics | | | | |
|------------------------|-----------------------|-----------|-----------|--|
| Wire size | | | | |
| | IEC | UL | CSA | |
| | NFC | DIN | | |
| Compression Solid wire | 0,5-4 mm ² | 24-12 AWG | 24-12 AWG | |
| clamp Stranded wire | 0,5-4 mm ² | 24-12 AWG | 24-12 AWG | |

| Characteristics | | | | |
|------------------------|-----------------------|-----------|-----|--|
| Wire size | | | | |
| | IEC | UL | CSA | |
| | NFC | DIN | | |
| Compression Solid wire | 0,5-4 mm ² | 22-10 AWG | | |
| clamp Stranded wire | 0,5-4 mm ² | 22-10 AWG | | |

| Characteristics | | | | |
|------------------------|-------------------------|-----------|-----------|--|
| Wire size | | | | |
| | IEC | UL | CSA | |
| | NFC | DIN | | |
| Compression Solid wire | 0,5-4 mm ² | 22-10 AWG | 20-12 AWG | |
| clamp Stranded wire | 0,5-2,5 mm ² | 22-10 AWG | 20-12 AWG | |

| Voltage | | | | |
|------------------|-------|-------|-------|--|
| Rated | 320 V | 600 V | 150 V | |
| Pulse | 4 kV | | | |
| Pollution degree | 3 | | | |

| Voltage | | | | |
|------------------|-------|-------|--|--|
| Rated | 320 V | 300 V | | |
| Pulse | 4 kV | | | |
| Pollution degree | 3 | | | |

| Voltage | | | | |
|------------------|-------|-------|-------|--|
| Rated | 400 V | 300 V | 300 V | |
| Pulse | 4 kV | | | |
| Pollution degree | 3 | | | |

| Current | | | | |
|---------|------|------|------|--|
| Rated | 10 A | 15 A | 10 A | |

| Current | | | | |
|---------|------|------|--|--|
| Rated | 10 A | 10 A | | |

| Current | | | | |
|---------|------|------|------|--|
| Rated | 10 A | 10 A | 10 A | |

| Wire size | | | | |
|-----------------------|------------------------|-----------------------------|-----------------|--|
| Rated / Gauge | 4 mm ² / A3 | 12 AWG | 12 AWG | |
| Wire stripping length | Recomm. screwdriver | Recomm. torque | Protection | |
| 10 mm .39" | 3,5 mm .16" | 0,4-0,6 Nm 3,5-5,3 lb.in | IP 20 NEMA 1 | |

| Wire size | | | | |
|-----------------------|------------------------|-----------------------------|-----------------|--|
| Rated / Gauge | 4 mm ² / A4 | 10 AWG | | |
| Wire stripping length | Recomm. screwdriver | Recomm. torque | Protection | |
| 9,5 mm .374" | 4 mm .157" | 0,5-0,6 Nm 4,4-5,3 lb.in | IP 20 NEMA 1 | |

| Wire size | | | | |
|-----------------------|--------------------------|-----------------------------|-----------------|--|
| Rated / Gauge | 2,5 mm ² / A4 | 10 AWG | 12 AWG | |
| Wire stripping length | Recomm. screwdriver | Recomm. torque | Protection | |
| 9,5 mm .37" | 4 mm .16" | 0,5-0,6 Nm 4,4-5,3 lb.in | IP 20 NEMA 1 | |

| Type | Part numbers |
|------------|------------------------|
| FEM6 | th. 2,8 mm 0118 368.16 |
| SCF6 | th. 3,0 mm 0118 707.03 |
| SCF6 | th. 3,0 mm 0128 707.05 |
| SCF6 V0 | th. 3,0 mm 0198 707.04 |
| SCFM6 | th. 3,0 mm 0114 825.05 |
| SCFEX1 (1) | th. 2,4 mm 0103 619.04 |
| SCFEX3 (1) | th. 2,4 mm 0103 620.01 |
| CBM5 | th. 0,5 mm 0178 745.14 |
| CBM8 | th. 0,8 mm 0178 746.15 |

| Type | Part numbers |
|------------|------------------------|
| FEM62 | th. 3 mm 0114 994.07 |
| SCFM6 | th. 3 mm 0114 825.05 |
| SCFEX1 (1) | th. 2,4 mm 0103 619.04 |
| SCFEX3 (1) | th. 2,4 mm 0103 620.01 |
| FC2 | DIA. 2 mm 0007 865.26 |
| CBM5 | th. 0,5 mm 0178 745.14 |
| CBM8 | th. 0,8 mm 0178 746.15 |
| PC61 | 10 poles 0163 311.22 |
| AD2,5 | 0114 205.20 |

| Type | Part numbers |
|------------|------------------------|
| FEM62 | th. 3 mm 0114 994.07 |
| FEM62 | th. 3 mm 0103 612.25 |
| FEM62 V0 | th. 3 mm 0194 994.00 |
| SCFM6 | th. 3 mm 0114 825.05 |
| SCFEX1 (1) | th. 2,4 mm 0103 619.04 |
| SCFEX3 (1) | th. 2,4 mm 0103 620.01 |
| FC2 | DIA. 2 mm 0007 865.26 |
| CBM5 | th. 0,5 mm 0178 745.14 |
| CBM8 | th. 0,8 mm 0178 746.15 |
| PC61 | 10 poles 0163 311.22 |
| AD2,5 | 0114 205.20 |
| DCJ | yellow 0173 059.03 |

(10) Sides of block (6) RC510 on blade
Note : (1) End sections and separators snapped on rails.

(11) Sides of block (6) RC810 on blade

(11) Sides of block