




A1RFRD10



REVISION RECORD				
REV	ECO	DESCRIPTION	DRFT	CHKD

NOTES:

ELECTRICAL:

1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 30 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH: 1000 VAC RMS 60Hz, 1MIN.

MECHANICAL:

1. HOUSING MATERIAL: GLASS FILLED POLYESTER UL 94V-0.
2. CONTACT MATERIAL: PHOSPHOR BRONZE $\phi 0.46$ MM
3. PLATING: GOLD PLATING OVER NICKEL.
4. OPERATING LIFE: 750 CYCLES MIN.
5. PCB RETENTION PRE-SOLDER: 1 LB MIN
6. PCB RETENTION POST-SOLDER: 10 LBS MIN.

ENVIRONMENTAL:

1. STORAGE: -40°C TO $+85^{\circ}\text{C}$.
2. OPERATION: -40°C TO $+85^{\circ}\text{C}$.

MATES WITH MODULAR PLUG CONFORMING TO
FCC PART 68, SUBPART F.

CUL FILE NO. E163191


PART NUMBER: E560X-00C06X

NO. OF CONTACT

8-8 CONTACTS

1- 10 CONTACTS

1- 3u" 2- 6u" 3-15u"
4-30u" 5-50u" 6-Pd20u"



PCB Layout $t=1.6$ MM

Component Side Shown

DETACHED LEFT	DATE 12/23/03	FULL RISE ELECTRONIC CO., LTD	
	DATE 12/23/03	TITLE 11.5 SIDE ENTRY	
	DATE 12/23/03	PCB GANG JACK 10P	
	DATE 12/23/03	DRAWING NO. GE563A88	
TOLERANCES EXCEPT AS NOTED		/PART NO. SEE NOTE	
MATERIAL :		SIZE A3	
QTY :		REV 0	
FINISH		DO NOT SCALE DRAWING	
SCALE : 2:1		SHEET 1 OF 1	

8

7

6

5

4

3

2

1