


HFI 140 // D-T 2/3/4

HFI 140 insulated twisted pairs, triples & quads
Intended for use as internal wiring of equipment

Description	Cores				Finished Cable					
D-T	No. of cores	Tin Plated Copper (TPC)			HFI 140	N/A	None	Weight	Amps	
		Size	Stranding	Conductor	Insulation	Shield/s	Sheath/s			
600 / 1000V AC U ₀ /U	Lay up	mm ²	# x mm	Nom Ø	Nom Ø	Nom Ø	Nom Ø	Nom g/m	@ 40°C	Article Number
D 3007 T 2	2	30	7 x 0.10	0.30	0.70	-	1.40	2.0	4	70300002006
D 2807 T 2		28	7 x 0.12	0.38	0.78	-	1.55	3.0	5	70300002008
D 2619 T 2		26	19 x 0.10	0.48	0.88	-	1.75	6.0	7	70300002015
D 2419 T 2		24	19 x 0.12	0.60	1.00	-	2.00	7.0	8	70300002020
D 2219 T 2		22	19 x 0.15	0.76	1.16	-	2.30	10	11	70300002040
D 2019 T 2		20	19 x 0.20	0.96	1.36	-	2.70	15	16	70300002060
D 1819 T 2		18	19 x 0.25	1.20	1.60	-	3.20	21	21	70300002100
D 1619 T 2		16	19 x 0.30	1.42	1.82	-	3.65	33	27	70300002120
D 1437 T 2		14	37 x 0.25	1.75	2.25	-	4.50	42	33	70300002200
D 1237 T 2		12	37 x 0.30	2.10	2.60	-	5.10	54	42	70300002260
D 3007 T 3	3	30	7 x 0.10	0.30	0.70	-	1.50	3.0	3	70300003006
D 2807 T 3		28	7 x 0.12	0.38	0.78	-	1.70	5.0	4	70300003008
D 2619 T 3		26	19 x 0.10	0.48	0.88	-	1.90	9.0	6	70300003015
D 2419 T 3		24	19 x 0.12	0.60	1.00	-	2.15	11	8	70300003020
D 2219 T 3		22	19 x 0.15	0.76	1.16	-	2.50	15	10	70300003040
D 2019 T 3		20	19 x 0.20	0.96	1.36	-	2.95	23	15	70300003060
D 1819 T 3		18	19 x 0.25	1.20	1.60	-	3.45	32	19	70300003100
D 1619 T 3		16	19 x 0.30	1.42	1.82	-	3.90	50	24	70300003120
D 1437 T 3		14	37 x 0.25	1.75	2.25	-	4.85	63	30	70300003200
D 1237 T 3		12	37 x 0.30	2.10	2.60	-	5.60	81	38	70300003260
D 3007 T 4	4	30	7 x 0.10	0.30	0.70	-	1.70	4.0	3	70300004006
D 2807 T 4		28	7 x 0.12	0.38	0.78	-	1.90	6.0	4	70300004008
D 2619 T 4		26	19 x 0.10	0.48	0.88	-	2.10	12	6	70300004015
D 2419 T 4		24	19 x 0.12	0.60	1.00	-	2.40	14	7	70300004020
D 2219 T 4		22	19 x 0.15	0.76	1.16	-	2.80	20	9	70300004040
D 2019 T 4		20	19 x 0.20	0.96	1.36	-	3.30	30	14	70300004060
D 1819 T 4		18	19 x 0.25	1.20	1.60	-	3.80	42	18	70300004100
D 1619 T 4		16	19 x 0.30	1.42	1.82	-	4.40	66	23	70300004120
D 1437 T 4		14	37 x 0.25	1.75	2.25	-	5.40	84	28	70300004200
D 1237 T 4		12	37 x 0.30	2.10	2.60	-	6.30	108	36	70300004260

Cable identification											
Cores: 1 st : Red, 2 nd : Blue, 3 rd : Yellow, 4 th : Green											
Characteristics and key properties											
	RoHS 2011/65/EU	REACH EC No. 1907/2006	LVD 2014/35/EU				Halogen free	Low smoke generation	Flame retardant	+120°C High temp	
DSP 61-12 Part 18 approved (Cores)							Test voltage 1.5 kV AC		Current rating in free air to IEC 60287	-30°C Low temp	

Data indicates nominal values in millimetres (mm) unless otherwise stated.
DISCLAIMER: Information is indicative and cannot be considered a binding representation or warranty for products and their use. Valid at the time of publication, it is subject to change without notice.