








Modular Contact, 2.00 Pitch

164-19203-311-E

KOBICONN

Modular Contact, 2.00 Pitch



Dimensions: mm

MATERIAL SPECIFICATIONS

Terminal:	Copper alloy
Housing:	Thermoplastic, Black
Finish:	Underplating nickel plating for all 50µ" min.
Solder Tail:	Plating tin (lead free) plating 100µ" min.
Contact:	Area is plated with 10µ" gold

ELECTRICAL SPECIFICATIONS

Current Rating:	1.0A AC/DC
Voltage Rating:	250V AC/DC
Contact Resistance:	30mΩ Max.
Insulation Resistance:	1000MΩ Min.
Withstanding Voltage:	500 V AC/minute
RoHS Compliant	

Date Last Revised: 06/29/12

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301269

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

164-19203-311-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[164-19203-311-E](#)