


OMNIMATE Signal - series BL/SL 5.08
SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Male connector for through-panel mounting with optional locking function. Internal connection as flat-blade or solder connection. These male connectors provide space for labelling and can be coded.

- 400 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

General ordering data

Type	SLDF 5.08 L/F 5 SN OR BX
Order No.	1599160000
Version	PCB plug-in connector, male header, 5.08 mm, No. of poles: 5, 180°, Flat-blade connection, Solder connection, Box
GTIN (EAN)	4008190079970
Qty.	50 pc(s).
Product data	IEC: 400 V / 15 A UL: 300 V / 10 A
Packaging	Box

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 6.88 g

System parameters

Product family	OMNIMATE Signal - series BL/SL 5.08	Wire connection method	Flat-blade connection, Solder connection
Conductor outlet direction	180°	Pitch in mm (P)	5.08 mm
Pitch in inches (P)	0.2 inch	No. of poles	5
L1 in mm	20.32 mm	L1 in inches	0.8 inch

Material data

Insulating material	PBT	Colour	Orange
Colour chart (similar)	RAL 2000	UL 94 flammability rating	V-0
CTI	≥ 200	Contact material	CuSn
Contact surface	tinned	Operating temperature, min.	-50 °C
Operating temperature, max.	100 °C	Temperature range, installation, min.	-25 °C
Temperature range, installation, max.	100 °C		

Rating data acc. to IEC 60664-1 / IEC 61984

Rated current, min. no. of poles (Tu=20°C)	15 A	Rated current, number of poles (Tu=40°C), min	13 A
Rated voltage for surge voltage class / pollution degree II/2	400 V	Rated voltage for surge voltage class / pollution degree III/2	320 V
Rated voltage for surge voltage class / pollution degree III/3	250 V	Rated impulse voltage for surge voltage class/ pollution degree II/2	4 kV
Rated impulse voltage for surge voltage class/ pollution degree III/2	4 kV	Rated impulse voltage for surge voltage class/ contamination degree III/3	4 kV

CSA rating data

Institute (CSA)		Certificate No. (CSA)	200039-1121690
Rated voltage (Use group B)	300 V	Rated current (use group B)	10 A
Rated voltage (use group D)	300 V	Rated current (use group D)	10 A

UL 1059 rating data

Institute (UR)		Certificate No. (UR)	E60693
Rated voltage (use group B)	300 V	Rated current (use group B)	10 A
Rated voltage (use group D)	300 V	Rated current (use group D)	10 A

Classifications

ETIM 3.0	EC001284	UNSPSC	30-21-18-10
eClass 5.1	27-26-07-04	eClass 6.2	27-26-07-04
eClass 7.1	27-44-04-02		

OMNIMATE Signal - series BL/SL 5.08 SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data

Notes

Notes

- Additional colours on request
- Rated current related to rated cross-section & min. No. of poles.
- Connectable cables with solder connection solid and flexible up to 2.5 mm² with insulating/shrink-wrap sleeve or from 2.8 mm flat blade receptacles with insulated sleeves acc. to DIN IEC 760
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

Approvals

Approvals




ROHS

Conform

OMNIMATE Signal - series BL/SL 5.08
SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (conditionally pluggable)

BLZ 5.08/180B



Female plugs with clamping-yoke screw for wire connection with straight (180°) outlet direction. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Delivery status Available until	Type	Order No.	Version	GTIN (EAN)	Qty.
This article will no longer be available in the future.	BLZ 5.08/05/180B SN OR BX	1529060000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190155308	50 pc(s).
2009-12-31T00:00:00	BLZ 5.08/05/180B SN BK BX	1529010000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	400819012518950	50 pc(s).
					IEC: 400 V / 19 A / 0.2 - 2.5 mm ² UL: 300 V / 15 A / 26 - 12 AWG

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

ZZ_Varianten



Female plugs with clamping-yoke screw for wire connection with straight (180°) outlet direction. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLZ	1529050000	PCB plug-in connector,	4008190290214	50 pc(s).	IEC: 400 V / 19 A / 0.2 - 2.5 mm ²	Box
5.08/05/180B		female plug, 5.08 mm, No.			UL: 300 V / 15 A / AWG 26 - AWG 12	
SN DKGX BX		of poles: 5, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box				

BLZF 5.08/180B



Female plugs with tension-clamp wire connection system, straight 180° outlet direction. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 17 A (IEC) / 15 A (UL)

General ordering data

Delivery status	Available until	Type	Order No.	Version	GTIN (EAN)	Qty.
This article will no longer be available in the future.	2015-12-31T00:00:00+01:00	BLZF 5.08/05/180B SN OR BX	1708330000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190317799	66 pc(s).

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (conditionally pluggable)

BLL 5.08/180B



Female header for PCB mounting. The solder pin length is optimised for wave flow soldering.

- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLL	1682760000	PCB plug-in connector, female header, Dovetails for fixing blocks, Solder connection, 5.08 mm, No. of poles: 5, 180°, Solder pin length (l): 3.2 mm, tinned, Orange, Box	4008190474522	66 pc(s).	IEC: 400 V / 23 A UL: 300 V / 15 A	Box
5.08/05/180B						
3.2SN OR BX						

BLDT 5.08B



Female plugs with two clamping-yoke screw connections per pole for wire connections with 90° and 270° outlet directions. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 14 A (IEC) / 10 A (UL)

General ordering data

Available until	Type	Order No.	Version	GTIN (EAN)	Qty.	Product data
2014-05-20	BLDT 5.08/05/270-B SN BK BX	1673810000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, TOP connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190435547	55 pc(s).	IEC: 400 V / 14 A / 0.2 - 2.5 mm ² UL: 300 V / 10 A / 26

OMNIMATE Signal - series BL/SL 5.08


SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

BLDT	1651770000	PCB plug-in connector,	4008190400453 55 pc(s).	IEC: 400 V / 14 A / 0.2 - 2.5 mm ²	-
5.08/05/-B		female plug, 5.08 mm,		UL: 300 V / 10 A / AWG 26 - AWG 12	AWG 12
SN OR BX		No. of poles: 5, 180°, TOP connection, Clamping range, rated connection, max.: 3.31 mm ² , Box			Box

BLZ 5.08/90B



Female plugs with clamping-yoke screw connection. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

General ordering data

Available until	Type	Order No.	Version	GTIN (EAN)	Qty.	Product data
2009-12-31T00:00:00	BLZ 5.08/05/90B SN BK BX	1555310000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 90°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190267971 66 pc(s).		IEC: 400 V / 15 A / 0.2 - 2.5 mm ² UL: 300 V / 10 A / AWG 26 - AWG 12
This article will no longer be available in the future.	2015-12-31T00:00:00+01:00	BLZ 5.08/05/90B SN OR BX	1555360000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 90°, Clamping yoke connection, Clamping range, rated connection,	4008190014902	66 pc(s).

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (conditionally pluggable)

max.: 3.31 mm²,
 Box

BLZ 5.08/225B



Female plugs with clamping-yoke screw for wire connection with 225° outlet direction. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 16.5 A (IEC) / 10 A (UL)

General ordering data

Delivery status Available until	Type	Order No.	Version	GTIN (EAN)	Qty.
This article will no longer be available in the future.	BLZ 5.08/05/225B SN OR BX	1742130000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 225°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190246778	66 pc(s).
2011-09-30 to 2015-09-30	BLZ 5.08/05/225B SN BK BX	1742360000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 225°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	403224804979066	66 pc(s).
					IEC: 400 V / 16.5 A / 0.2 - 2.5 mm ² UL: 300 V / 10 A / AWG 26 - 12 AWG

OMNIMATE Signal - series BL/SL 5.08 SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

BLZ 5.08/270B



Female plugs with clamping-yoke screw connection. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

General ordering data

Available until	Type	Order No.	Version	GTIN (EAN)	Qty.	Product data
2009-12-31T00:00:00	BLZ 5.08/05/270B SN BK BX	1559910000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 270°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190269685	66 pc(s).	IEC: 400 V / 15 A / 0.2 - 2.5 mm ² UL: 300 V / 10 A / 26 - 12 AWG
This article will no longer be available in the future.	2015-12-31T00:00:00+01:00	BLZ 5.08/05/270B SN OR BX	1559960000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 270°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190123253	66 pc(s).

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

BLZF 5.08/270B



Female plugs with tension-clamp wire connection system. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 16.5 A (IEC) / 10 A (UL)

General ordering data

Available until	Type	Order No.	Version	GTIN (EAN)	Qty.	Product data
2011-09-30	BLZF 5.08/270B SN BK BX	1672660000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 270°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190434373	66 pc(s).	IEC: 400 V / 16.5 A / 0.2 - 2.5 mm ² UL: 300 V / 10 A / 26 - 12 AWG
This article will no longer be available in the future.	2015-12-31	BLZF 5.08/05/270B SN OR BX	1672430000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 270°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190434144	66 pc(s).

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (conditionally pluggable)

BLZP 5.08/225B SN




Clamping-yoke wire connection with right-angled (90° or 270°) or angled (225°) outlet direction. The female plugs provide space for labelling and can be coded. Can be fastened with flange or release latch. They also feature the integrated plus/minus screw, protection from under insertion of wire, and are delivered with open clamping yoke.

- 0.2 – 2.5 mm² (IEC) / 26-12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 17.5 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLZP	1946010000	PCB plug-in connector,	4032248621538	66 pc(s).	IEC: 400 V / 17.5 A / 0.2 - 4 mm ²	Box
5.08HC/05/225B		female plug, 5.08 mm, No.			UL: 300 V / 15 A / AWG 30 - AWG 12	
SN BK BX		of poles: 5, 225°, Clamping yoke connection, Clamping range, rated connection, max.: 4 mm ² , Box				
BLZP	1945780000	PCB plug-in connector,	4032248621255	66 pc(s).	IEC: 400 V / 17.5 A / 0.2 - 4 mm ²	Box
5.08HC/05/225B		female plug, 5.08 mm, No.			UL: 300 V / 15 A / AWG 30 - AWG 12	
SN OR BX		of poles: 5, 225°, Clamping yoke connection, Clamping range, rated connection, max.: 4 mm ² , Box				

BLC 5.08BR



Female plugs with crimp wire connection system. The female plugs provide space for labelling and can be coded.

- 0.25 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 21 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLC	1649400000	PCB plug-in connector,	4008190294519	50 pc(s).	IEC: 400 V / 21 A	Box
5.08/05/180BR		female plug, 5.08 mm, No.			UL: 300 V / 10 A / AWG 26 - AWG 14	
OR BX		of poles: 5, 180°, Crimp connection, Clamping range, rated connection, max.: 2.5 mm ² , Box				
BLC	1712140000	PCB plug-in connector,	4008190935153	50 pc(s).	IEC: 400 V / 21 A	Box
5.08/05/180BR		female plug, 5.08 mm, No.			UL: 300 V / 10 A / AWG 26 - AWG 14	
BK BX		of poles: 5, 180°, Crimp connection, Clamping				

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (conditionally pluggable)

range, rated connection,
 max.: 2.5 mm², Box

BLZF 5.08/90B



Female plugs with tension-clamp wire connection system. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 16.5 A (IEC) / 10 A (UL)

General ordering data

Delivery status Available until	Type	Order No.	Version	GTIN (EAN)	Qty.
This article will no longer be available in the future.	BLZF 5.08/05/90B SN OR BX	1671280000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 90°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190432980	66 pc(s).
2011-09-30	BLZF 5.08/26/90B SN BK BX	1671510000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 90°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	400819043321566	IEC: 400 V / 16.5 A / 0.2 - 2.5 mm ² UL: 300 V / 10 A / 26 AWG 12

OMNIMATE Signal - series BL/SL 5.08 SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (fully pluggable)

BLZP 5.08/225 SN



Clamping-yoke wire connection with right-angled (90° or 270°) or angled (225°) outlet direction. The female plugs provide space for labelling and can be coded. Can be fastened with flange or release latch. They also feature the integrated plus/minus screw, protection from under insertion of wire, and are delivered with open clamping yoke.

- 0.2 – 2.5 mm² (IEC) / 26-12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 17.5 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLZP 5.08HC/05/225 SN OR BX	1946280000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 225°, Clamping yoke connection, Clamping range, rated connection, max.: 4 mm ² , Box	4032248621859	72 pc(s).	IEC: 400 V / 17.5 A / 0.2 - 4 mm ² UL: 300 V / 15 A / AWG 30 - AWG 12	Box
BLZP 5.08HC/05/225 SN BK BX	1946590000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 225°, Clamping yoke connection, Clamping range, rated connection, max.: 4 mm ² , Box	4032248622368	72 pc(s).	IEC: 400 V / 17.5 A / 0.2 - 4 mm ² UL: 300 V / 15 A / AWG 30 - AWG 12	Box

BLDZ DN 5.08F AU



Female plugs with two clamping-yoke screw connections per pole. The integrated cross-connection enables the signals (e.g. DeviceNet) to be looped through securely. The T-type arrangement of the connections enables individual modules to be decoupled easily from the network. The test point enables manual diagnosis. The gold-plated contact system guarantees up to 1,000 plugging/unplugging operations!

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLDZ DN5.08/05/180F GY BX PRT	1919990000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 2.5 mm ² , Box	4032248557899	50 pc(s).	IEC: 400 V / 16 A / 0.2 - 2.5 mm ² UL: 300 V / 15 A / AWG 22 - AWG 12	Box

OMNIMATE Signal - series BL/SL 5.08 SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (fully pluggable)

BLL 5.08/90




Female header for PCB mounting. The solder pin length is optimised for wave flow soldering.

- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLL	1622970000	PCB plug-in connector,	4008190194017	72 pc(s).	IEC: 400 V / 23 A	Box
5.08/05/90		female header, closed side,			UL: 300 V / 15 A	
3.2 SN OR BX		Solder connection, 5.08 mm, No. of poles: 5, 90°, Solder pin length (l): 3.2 mm, tinned, Orange, Box				

BLT 5.08



Female plugs with TOP screw system for connecting wires with straight 180° outlet direction. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 17 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLT	1499810000	PCB plug-in connector,	4008190861728	72 pc(s).	IEC: 400 V / 17 A / 0.2 - 2.5 mm ²	Box
5.08HC/05/180		female plug, 5.08 mm,			UL: 300 V / 13 A / AWG 26 - AWG 14	
SN BK BX		No. of poles: 5, 180°, TOP connection, Clamping range, rated connection, max.: 2.5 mm ² , Box				
BLT	1499860000	PCB plug-in connector,	4008190030285	72 pc(s).	IEC: 400 V / 17 A / 0.2 - 2.5 mm ²	Box
5.08HC/05/180		female plug, 5.08 mm,			UL: 300 V / 13 A / AWG 26 - AWG 14	
SN OR BX		No. of poles: 5, 180°, TOP connection, Clamping range, rated connection, max.: 2.5 mm ² , Box				

OMNIMATE Signal - series BL/SL 5.08 SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (fully pluggable)

BLL 5.08/180



Female header for PCB mounting. The solder pin length is optimised for wave flow soldering.

- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLL	1630740000	PCB plug-in connector,	4008190204167 72 pc(s).		IEC: 400 V / 23 A	Box
5.08/05/180		female header, closed side,			UL: 300 V / 15 A	
3.2 SN OR BX		Solder connection, 5.08 mm, No. of poles: 5, 180°, Solder pin length (l): 3.2 mm, tinned, Orange, Box				

BLIDC 5.08



Female plugs with IDC wire connection system. The female plugs provide space for labelling and can be coded.

- 0.35 - 0.75 mm² (IEC) / 22 - 20 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 11 A (IEC) / 5 A (UL)

General ordering data

Available until	Type	Order No.	Version	GTIN (EAN)	Qty.	Product data
2009-12-31	BLIDC 5.08/05/180 SN OR BX	1724970000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, IDC terminal, Clamping range, rated connection, max.: 0.75 mm ² , Box	4008190377311 50 pc(s).		IEC: 400 V / 11 A / 0.5 - 0.75 mm ² UL: 300 V / 5 A / AWG 22 -

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (fully pluggable)

AWG
20

BLZP 5.08/180 SN



Female plugs with clamping-yoke screw for wire connection with straight (180°) outlet direction. The female plugs provide space for labelling and can be coded. Can be fastened with flange or release latch. They also feature the integrated plus/minus screw, protection from under insertion of wire, and are delivered with open clamping yoke.

- 0.2 – 2.5 mm² (IEC) / 26-12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLZP 5.08HC/05/180 SN BK BX	1943840000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 4 mm ² , Box	4032248617876 45 pc(s).		IEC: 400 V / 19 A / 0.2 - 4 mm ² UL: 300 V / 15 A / AWG 30 - AWG 12	Box
BLZP 5.08HC/05/180 SN OR BX	1943610000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 4 mm ² , Box	4032248617609 45 pc(s).		IEC: 400 V / 19 A / 0.2 - 4 mm ² UL: 300 V / 15 A / AWG 30 - AWG 12	Box

BLZF 5.08/270



Female plugs with tension-clamp wire connection system. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 16.5 A (IEC) / 10 A (UL)

General ordering data

Delivery status Available until	Type	Order No.	Version	GTIN (EAN)	Qty.
This article will no longer be available in the future.	BLZF 5.08/05/270 SN OR BX	1671970000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 270°, Tension clamp connection, Clamping range, rated connection,	4008190433680	72 pc(s).

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (fully pluggable)

This article will no longer be available in the future.	BLZF 5.08/05/270 SN BK BX	1672200000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 270°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm², Box	4008190433918	72 pc(s).

BLZF 5.08/180



Female plugs with tension-clamp wire connection system, straight 180° outlet direction. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 17 A (IEC) / 15 A (UL)

General ordering data

Delivery status	Available until	Type	Order No.	Version	GTIN (EAN)	Qty.
This article will no longer be available in the future.	2015-12-31T00:00:00+01:00	BLZF 5.08/05/180 SN BK	1707720000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm², Box	4008190316723	72 pc(s).
		BX				
This article will no longer be available in the future.	2015-12-31T00:00:00+01:00	BLZF 5.08/05/180 SN OR	1707490000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm², Box	4008190395865	72 pc(s).
		BX				

OMNIMATE Signal - series BL/SL 5.08 SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (fully pluggable)

BLZF 5.08/90



Female plugs with tension-clamp wire connection system. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 16.5 A (IEC) / 10 A (UL)

General ordering data

Delivery status	Available until	Type	Order No.	Version	GTIN (EAN)	Qty.
This article will no longer be available in the future.	2015-12-31T00:00:00+01:00	BLZF 5.08/05/90 SN OR BX	1670820000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 90°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190432423	72 pc(s).
This article will no longer be available in the future.	2015-12-31T00:00:00+01:00	BLZF 5.08/05/90 SN BK BX	1671050000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 90°, Tension clamp connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190432720	72 pc(s).

BLZ 5.08/225



Female plugs with clamping-yoke screw for wire connection with 225° outlet direction. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 16.5 A (IEC) / 10 A (UL)

General ordering data

Available until	Type	Order No.	Version	GTIN (EAN)	Qty.	Product data
2014-06-25T00:00:00+02:00	BLZ 5.08/05/225 SN BK BX	1741900000	PCB plug-in connector, female plug, 5.08 mm,	4008190255596	72 pc(s).	IEC: 400 V /

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (fully pluggable)

No. of poles: 5,	16.5
225°, Clamping	A /
yoke connection,	0.2
Clamping range,	-
rated connection,	2.5
max.: 3.31 mm²,	mm²
Box	UL:
	300
	V /
	10
	A /
	AWG
	26
	-
	AWG
	12

This article will no longer be available in the future.	2015-12-31T00:00:00+01:00	BLZ 5.08/05/225 SN OR BX	1741670000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 225°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm², Box	4032248049844	72 pc(s).
---	---------------------------	--------------------------	----------------------------	---	---------------	-----------

BLZP 5.08/270 SN



Female plugs with clamping-yoke screw connection for wire connection and a right-angle (90° or 270°) outlet direction. The female plugs provide space for labelling and can be coded. Can be fastened with flange or release latch. They feature an integrated plus/minus screw, protection against false insertion under clamping yoke. They are delivered with an opened clamping yoke.

- 0.2 – 2.5 mm² (IEC) / 26-12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLZP	1949050000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 270°, Clamping yoke connection, Clamping range, rated connection, max.: 4 mm², Box	4032248626502	72 pc(s).	IEC: 400 V / 15.5 A / 0.2 - 4 mm² UL: 300 V / 15 A / AWG 30 - AWG 12	Box
5.08HC/05/270 SN BK BX						
BLZP	1948820000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 270°, Clamping yoke connection, Clamping	4032248626274	72 pc(s).	IEC: 400 V / 15.5 A / 0.2 - 4 mm² UL: 300 V / 15 A / AWG 30 - AWG 12	Box
5.08HC/05/270 SN OR BX						

OMNIMATE Signal - series BL/SL 5.08


SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (fully pluggable)

range, rated connection,
 max.: 4 mm², Box

BLDT 5.08



Female plugs with two clamping-yoke screw connections per pole for wire connections with 90° and 270° outlet directions. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 14 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLDT 5.08/05/- SN OR BX	1644760000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, TOP connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190283971	50 pc(s).	IEC: 400 V / 14 A / 0.2 - 2.5 mm ² UL: 300 V / 10 A / AWG 26 - AWG 12	Box
BLDT 5.08/05/- SN BK BX	1660740000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, TOP connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190417192	60 pc(s).	IEC: 400 V / 14 A / 0.2 - 2.5 mm ² UL: 300 V / 10 A / AWG 26 - AWG 12	Box

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (fully pluggable)

BLF 5.08/90 SN




Just as reliable as the tried-and-tested original, with innovation in detail: the BLF 5.08, PUSH-IN version of the BLZ 5.08 female header, features a new connection system and a more compact design. Weidmüller innovative PUSH-IN spring connection features a trend-setting, tool-free wire connection system that is simple to operate. In terms of versatility, the BLF 5.08 offers just as much as the older versions:

- The choice of three wire outlet directions offers you proven design flexibility for your applications.
- Four flange variations, including the patented release latch, so you can design the interlock based on the requirements of the user.
- Use the BLF 5.08 and SL 5.08HC plug combination in order to reach the max. rated specifications.

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLF 5.08HC/05/90 SN OR BX	1001560000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 90°, PUSH IN spring connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4032248693368	72 pc(s).	IEC: 400 V / 24 A / 0.2 - 2.5 mm ² UL: 300 V / 18.5 A / AWG 26 - AWG 12	Box
BLF 5.08HC/05/90 SN BK BX	1000060001	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 90°, PUSH IN spring connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4032248689996	72 pc(s).	IEC: 400 V / 24 A / 0.2 - 2.5 mm ² UL: 300 V / 18.5 A / AWG 26 - AWG 12	Box

BLC 5.08R



Female plugs with crimp wire connection system. The female plugs provide space for labelling and can be coded.

- 0.25 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 21 A (IEC) / 10 A (UL)

General ordering data

Type	Order No.	Version	GTIN (EAN)	Qty.	Product data	Packaging
BLC 5.08/05/180R OR BX	1610520000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 180°, Crimp connection, Clamping	4008190017736	50 pc(s).	IEC: 400 V / 21 A UL: 300 V / 10 A / AWG 26 - AWG 14	Box

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (fully pluggable)

		range, rated connection, max.: 2.5 mm ² , Box			
BLC	1711990000	PCB plug-in connector,	4008190935009 50 pc(s).	IEC: 400 V / 21 A	Box
5.08/05/180R		female plug, 5.08 mm, No.		UL: 300 V / 10 A / AWG 26 - AWG 14	
BK BX		of poles: 5, 180°, Crimp connection, Clamping range, rated connection, max.: 2.5 mm ² , Box			

BLZ 5.08/270



Female plugs with clamping-yoke screw connection.
 The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

General ordering data

Delivery status Available until	Type	Order No.	Version	GTIN (EAN)	Qty.
This article will 2015-12-31T00:00:00+01:00 no longer be available in the future.	BLZ 5.08/05/270 SN BK BX	1557610000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 270°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190269456	72 pc(s).
This article will 2015-12-31T00:00:00+01:00 no longer be available in the future.	BLZ 5.08/05/270 SN OR BX	1557660000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 270°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190144012	72 pc(s).

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (fully pluggable)

BLZ 5.08/90



Female plugs with clamping-yoke screw connection. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

General ordering data

Delivery status Available until	Type	Order No.	Version	GTIN (EAN)	Qty.
This article will no longer be available in the future.	BLZ 5.08/05/90 SN OR BX	1553060000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 90°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190081331	72 pc(s).
This article will no longer be available in the future.	BLZ 5.08/05/90 SN BK BX	1553010000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5, 90°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm ² , Box	4008190267735	72 pc(s).

BLZ 5.08/180



Female plugs with clamping-yoke screw for wire connection with straight (180°) outlet direction. The female plugs provide space for labelling and can be coded.

- 0.2 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Delivery status Available until	Type	Order No.	Version	GTIN (EAN)	Qty.
This article will no longer be available in the future.	BLZ 5.08/05/180 SN OR BX	1526760000	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 5,	4008190052287	50 pc(s).

OMNIMATE Signal - series BL/SL 5.08

SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Mating connector (fully pluggable)

180°, Clamping
 yoke connection,
 Clamping range,
 rated connection,
 max.: 3.31 mm²,
 Box

This article will no longer be available in the future.	2015-12-31T00:00:00+01:00	BLZ 5.08/05/180 SN BK	1526710000	PCB plug-in	4008190287856	50
		BX		connector, female		pc(s).
				plug, 5.08 mm, No. of poles: 5, 180°, Clamping yoke connection, Clamping range, rated connection, max.: 3.31 mm², Box		

BL 5.08



Female plugs with leaf-spring wire connection system.
 The female plugs provide space for labelling.

- 0.2 - 1.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 11 A (IEC) / 10 A (UL)

General ordering data

Delivery status	Available until	Type	Order No.	Version	GTIN (EAN)	Qty.
This article will no longer be available in the future.	2015-12-31T00:00:00+01:00	BL 5.08/05/180 SN OR BX	1716350000	PCB plug-in	4008190376383	50
				connector, female		pc(s).
				plug, 5.08 mm, No. of poles: 5, 180°, Pressure clamp connection, Clamping range, rated connection, max.: 2.08 mm², Box		
This article will no longer be available in the future.	2015-12-31T00:00:00+01:00	BL 5.08/05/180 SN DKGX	1723860000	PCB plug-in	4008190376222	50
				connector, female		pc(s).
				plug, 5.08 mm, No. of poles: 5, 180°, Pressure clamp connection, Clamping range, rated connection, max.: 2.08 mm², Box		
This article will no longer be available in the future.	2015-12-31T00:00:00+01:00	BL 5.08/05/180 SN BK BX	1716500000	PCB plug-in	4008190376543	50
				connector, female		pc(s).
				plug, 5.08 mm,		

OMNIMATE Signal - series BL/SL 5.08 SLDF 5.08 L/F 5 SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Mating connector (fully pluggable)

available in the
future.

No. of poles: 5,
180°, Pressure
clamp connection,
Clamping range,
rated connection,
max.: 2.08 mm²,
Box

Addresses worldwide

Let's connect.

AE United Arab Emirates
Weidmüller Middle East FZE
Warehouse Q3-79
SAIF-Zone
P.O. BOX 8591
Sharjah
Tel. +971 65572723
Fax +971 65572724
wme.info@weidmueller.com

AO Angola
Please contact
Phambili Interface
South Africa

AR Argentina
CPI SA
Bauness 2660
C1431DOF Buenos Aires
Tel. +54 11 4523 8008
Fax +54 11 4522 0546
info@cpi.com.ar
www.cpi.com.ar

AT Austria
Weidmüller GmbH
IZ NOE Süd Straße 2b, Obj
M 59
2355 Wiener Neudorf
Tel. +43 2236 67080
Fax +43 2236 6708-899
office.at@weidmueller.com
www.weidmueller.com

AU Australia
Weidmüller Pty. Ltd.
PO BOX 6944
Huntingwood 2148
Huntingwood Drive 43
Huntingwood NSW 2148
Tel. +61 2 9671 9999
Fax +61 2 9671 9911
info@weidmuller.com.au
www.weidmuller.com.au

AZ Azerbaijan
Representative Office
Rashad Mahmudov
Demirchi Tower, 4th floor
37, Khojali ave.
AZ 1025 Baku
Tel. +994 12 488 80 36
Fax +994 12 488 80 37
rashad.mahmudov@weidmueller.com

BA Bosnia and Herzegovina
Please contact
our Representative Office
Weidmüller Interface GmbH
& Co. KG
Serbia

or
BIG electric d.o.o
Mladena Stojanovića 117A
78000 Banja Luka
Tel. +387 51926277
Fax +387 51926277
bigelectric@blic.net
www.bigelectric.ba

BE Belgium
Weidmüller Benelux B. V.
Mechelsesteenweg 519 bus
6 en 7
1930 Nossegem
Tel. +32 2 752 40 70
Fax +32 2 751 36 06
info@weidmueller.be
www.weidmueller.be

BG Bulgaria
Weid-Bul EOOD
Bul. „Kliment Ohridski“ 13
1756 Sofia
Tel. +359 2 963 2560
Fax +359 2 963 1098
sofia@weidbul.com
www.weidbul.com

BH Bahrain
Khayber Trading Company
P.O Box 1976
Manama
Tel. +973 720747
Fax +973 720331
khayber@batelco.com.bh

BR Brazil
Weidmüller Conexel do Brasil
Conexões Elétricas Ltda.
Av. Presidente Juscelino, 642
- Piraporinha
Diadema, São Paulo
09950-370
Tel. +55 (11) 4366-9600
Fax +55 (11) 4362-1677
vendas@weidmueller.com.br
www.weidmueller.com.br

BW Botswana
Please contact
Phambili Interface
South Africa

BY Belarus
TECHNIKON Ltd.
Nezavisimosti pr. 177-9
220125 Minsk
Tel. +375 17 393-11-77
Fax +375 17 3930080
wm@technikon.by

CA Canada
W Interconnections Canada
Inc.
10 Spy Court
Markham Ontario L3R 5H6
Tel. +1 (905) 475-1507
Ext. 9836
Fax +1 (905) 475-2798
support@weidmuller.ca
www.weidmuller.ca

CG Congo
Please contact
Phambili Interface
South Africa

CH Switzerland
Weidmüller Schweiz AG
Rundbuckstraße 2
8212 Neuhausen am
Rheinfall SH
Tel. +41 52 674 07 07
Fax +41 52 674 07 08
info@weidmueller.ch
www.weidmueller.ch

CL Chile
ATS-INTECH
Maria Luisa Santander 0475
Santiago
Providencia 7500859
Tel. +56 2 341 1271
Fax +56 2 341 1275
felipe@atsintech.com
www.atsintech.com
CPI CHILE LTDA
Av. Presidente Frei Montalva
6001, 47 complejo el cortijo
Santiago - Conchalí
Tel. +562 963 8440
Fax +562 963 8440
cpi@cpichile.cl
www.cpichile.cl

CN China
Weidmüller Interface
(Shanghai) Co. Ltd.
100 Yutong Road
25 F, BM Intercontinental
Business Center
200070 Shanghai
Tel. +86 21-22195008
Fax +86 21-22195009
customer.hotline@weidmueller.com.cn
www.cnweidmuller.com

CO Colombia
Automatización Avanzada
S. A.
Carrera 97 No., 24 c - 23
Bodega 4
110911 Bogotá-D.C.
Tel. +57 (1) 547-8510
Fax +57 (1) 422-3044
comercial@automatizacionavanzada.com
www.automatizacionavanzada.com

CR Costa Rica
ELVATRON S. A.
la Uruca 400 Norte Banco
Costa Rica
San Jose Costa Rica
Tel. +506 2961-060
Fax +506 5200-609
dirk.haase@elvatron.com
www.elvatron.com

CZ Czech Republic
Weidmüller s.r.o.
Lomnického 5/1705
140 00 Praha 4
Tel. +420 244 001 400
Fax +420 244 001 499
office@weidmueller.cz
www.weidmueller.cz

DE Germany
Weidmüller GmbH & Co. KG
Ohmstraße 9
32758 Detmold
Postfach 30 54
32720 Detmold
Tel. +49 5231 1428-0
Fax +49 5231 1428-116
weidmueller@weidmueller.de
www.weidmueller.de

DK Denmark
Weidmüller Danmark
Vallensbækvej 18A
2605 Brøndby
Tel. +45 27747800
kundeservice@weidmuller.dk
www.weidmuller.dk

EC Ecuador
Elsystec S. A., Electricidad
Sistemas y Tecnología
Vasco de Contreras N35-25 1
y Mañosa
Quito - Pichincha
Tel. +593 22456510
Fax +593 22456755
Elsystec@uio.satnet.net

EE Estonia
Please contact
our Representative Office
Weidmüller Interface GmbH
& Co. KG
Latvia

or

Soots Interface OÜ
Pärnu mnt 142
11317 Tallinn
Tel. +372 609 6933
Fax +372 609 6933
info@sootsinterface.ee
www.sootsinterface.ee

EG Egypt
Standard Electric (OMEGA)
87, Mohamed Farid Street
Heliopolis
Cairo
Tel. +202 26229000
Fax +202 26221555
stdelec@rite.com

ES Spain
Weidmüller, S. A.
Narcis Monturiol 11-13, Pol.
Ind. Sudoeste
8960 Sant Just
Desvern - Barcelona
Tel. +34 934 803 386
Fax +34 933 718 055
weidmuller@weidmuller.es
www.weidmuller.es

FI Finland
Weidmüller Suomi,
Weidmüller Aktiebolagetin
sivulike
Koy Plaza Vivace
Äyritie 8C
FI 1510 Vantaa
Tel. +358 20 7351300
Fax +358 800 114 667
asiakaspalvelu@weidmuller.fi
www.weidmuller.fi

FR France
Weidmüller E. U. R. L.
12, Chaussée Jules César
BP 263 Osny
95523 Cergy-Pontoise Cedex
Tel. +33 1 34 24 55 00
Fax +33 1 34 24 55 01
mail@weidmuller.fr

GB Great Britain
Weidmüller Ltd.
Klippon House
Centurion Court Office Park,
Meridian East, Meridian
Business Park
Leicester
LE19 1TP
Tel. +44 116 282 3470
Fax +44 116 289 3582
marketing@weidmuller.co.uk
www.weidmuller.co.uk

GE Georgia
Please contact
our Representative Office
Rashad Mahmudov
Azerbaijan.

GR Greece
G.A. Solutions
Ippokratous 11 Metamorfosi
144 52 Athen
Tel. +30 210 2823233
Fax +30 210 2823233
info@weidmuller.gr
www.weidmuller.gr

GT Guatemala
Prestelectro, Prestegard
Electro, S.A.
Avenida Petapa 44-22,
Zona 12
Guatemala City
Tel. +502 2442-3346
Fax +502 2476-8945
ventas@prestelectro.com

HK Hong Kong
Weidmüller (Hong Kong)
Limited Co. Ltd.
Unit 1617, Metropolis Tower
No. 10 Metropolis Drive,
Hunghom, Kowloon
Tel. +852 3154 8088
Fax +852 31548099
Info-hk@weidmueller.com.hk

HR Croatia
ElektroPARTNER d.o.o.
Slavonska avenija 24/6
HR-10000 Zagreb
Tel. +385 (1) 6184 793
Fax +385 (1) 6184 795
elektropartner@zg-tcom.hr
www.elektropartner.hr

HU Hungary
Weidmüller Kereskedelmi Kft.
Budapest
Gubacsi út 6.
1097
Tel. +36 1 382 7700
Fax +36 1 382 7701
info@weidmueller.hu
www.weidmueller.hu

ID Indonesia
PT. Nego Electrindo
Ruko Mega Grosir Cempaka
Mas Blok I No. 20 - 22
Jakarta 10640
Tel. +62 21 42882255
Fax +62 21 42882266
sales@negoelectrindo.co.id

IE Ireland
Please contact
Weidmüller Ltd.
Great Britain

IL Israel
A. U. Shay Ltd.
23/25, Embar Street
49222 Petach-Tikva
P.O. Box 1 00 49
49222 Petach-Tikva
Tel. +972 3-923-3601
Fax +972 3-923-4601
shay@uriel-shay.com
www.uriel-shay.com
ATEKA Ltd.
4, Ha Tavor lane Industrial
area Segula
49691 Petach-Tikva
P.O. Box 4710
Petach-Tikva
Tel. +972 73-200-1311
Fax +972 3-924 4245
marketing@ateka.co.il
www.ateka.co.il

IN India
Representative Office
Weidmüller Electronics India
Pvt. Ltd.
12th Lane North Avenue, Opp
Joggers Park,
Kalyani Nagar, Pune
411 006
Tel. +91 20-41290090
Nitish.Rajan@weidmueller.de
www.weidmueller.com

IS Iceland
Samey Automation Center
Lyngas 13
210 Garoabaer
Tel. +354 510 5200
Fax +354 510 5201
Samey@samey.is
www.samey.is

IT Italy
Weidmüller S. r.l.
Via Albert Einstein 4
20092 Cinisello
Balsamo Milano
Tel. +39 02 660681
Fax +39 02 6124945
weidmuller@weidmuller.it
www.weidmuller.it

JM Jamaica
Please contact
W Interconnections Inc.
United States

JO Jordan
Trans Jordan for Electro
PO Box 33 06 07
Amman
Tel. +962 6 533 2020
Fax +962 6 533 5800
transjordan@batelco.jo

JP Japan
Nihon Weidmüller Co. Ltd.
Sphere Tower Tennoz 2-2-8
Higashi-Shinagawa,
Shinagawa-ku
Tokyo
140-0002
Tel. +81 3 6711 5300
Fax +81 3 6711 5333
weidmullerjapan@weidmuller.co.jp
www.weidmuller.co.jp

KE Kenya
Please contact
Phambili Interface
South Africa

KR Korea
Weidmüller Korea Co. Ltd.
9th floor, Wonbang B/D
Samseong 2-Dong, Gangnam-Gu
Seoul 143-42
Tel. +82 2-516-0003
Fax +82 2-516-0090
info@weidmuller.co.kr
www.weidmuller.co.kr

KZ Kazakhstan
Please contact
OOO Weidmüller
Russia

LT Lithuania
Please contact
our Representative Office
Weidmüller Interface GmbH
& Co. KG
Latvia

or
ELEKTROS IRANGA
Tinklų g. 29 a
LT-5319 Panevezys
Tel. +370 (45) 582 828
Fax +370 (45) 582 727
info@eliranga.lt

LU Luxembourg
Please contact
Weidmüller Benelux B. V.
Netherlands



You can find all Weidmüller addresses and your local contact on the internet at: www.weidmueller.com/countries

Let's connect.

Sales company 

Representation abroad 

without representation abroad 

LV Latvia SIA Abi4 Daugavgrivas 31b Riga, LV-1007 Tel. +371 674 70999 Fax +371 674 65637 abi_4@tvnet.lv Representative Office Weidmüller Interface GmbH & Co. KG Udens str. 12-118 Riga, LV-1007 Tel. +371 29254766 Fax +371 676 24562 lgonis.rudaks@weidmueller.com www.weidmueller.com	MZ Mozambique Please contact Phambili Interface South Africa	PK Pakistan Automation Controls (Pak) Apartment No. 33 C III, Chenab Block, Allama Iqbal Town Lahore Tel. +92 42 37809948 Fax +92 42 37809950 nadeem@acpak.com.pk www.acpak.com.pk	SI Slovenia Elektrospoji d. o. o. Stegne 27 SI- 1000 Ljubljana Osrednjeslovenska Tel. +386 1 511 3810 Fax +386 1 511 1604 info@elektrospoji.si www.elektrospoji.si	UA Ukraine LLC WM UKRAINE Levanevskogo str. 6 Kiev 3058 Tel. +38 044 490 32 48 Fax +38 044 490 32 49 info@wm-ua.com.ua wm-ua.com.ua/ Representative Office Weidmüller Interface GmbH & Co. KG Z. office 303 7-D, Zdobunivska str. Kiev, 2081 Mobile +38 050 440 25 24 info.ua@weidmueller.com
MD Moldova BERHORD A & D srl 79/1, str. Milescu Spartaru MD-2075 Chisinau Moldova Tel. +373 (22) 815002 Fax +373 (22) 815007 atiuleanu@berhord.com www.ad.berhord.com	NG Nigeria Please contact Phambili Interface South Africa	PL Poland Weidmüller Sp. z o. o. ul. Ogrodowa 58 00-876 Warszawa Tel. +48 22 510 09 40 Fax +48 22 510 09 41 biuro@weidmuller.com.pl www.weidmuller.pl	SK Slovakia ELEKTRIS s.r.o. Elektrárnská 1 831 04 Bratislava Tel. +421 2/4920 0113 Fax +421 2/4920 0119 bratislava@elektris.sk	US United States W Interconnections Inc. 821 Southlake Boulevard Richmond Virginia 23236 Tel. +1 (804) 794-2877 Fax +1 (804) 379-2593 info@weidmuller.com www.weidmuller.com
ME Montenegro Please contact our Representative Office Weidmüller Interface GmbH & Co. KG Serbia.	NL Netherlands Weidmüller Benelux B. V. Franciscusweg 221 1216 SE Hilversum P.O. Box 1505 1200 BM Hilversum Tel. +31 35 626 12 61 Fax +31 35 623 20 44 info@weidmuller.nl www.weidmuller.nl	PR Puerto Rico Please contact W Interconnections Inc. United States	SV El Salvador Prestegard Electro 11 Avenida Norte No. 240 Edificio Salazar No. 2 San Salvador Tel. +503 2271 1690 Fax +503 2221 3851 prestegard@navegante.com.sv	UZ Republic of Uzbekistan Please contact OOO Weidmüller Russia
MG Madagascar Please contact Phambili Interface South Africa	NO Norway Sivilingeniør J.F. Knudtzen AS Billingstadsletta 97 1396 Billingstad PO Box 160 1378 Nesbru Tel. +47 66 98 33 50 Fax +47 66 98 09 55 firmapost@jfkudtzen.no www.jfkudtzen.no	PT Portugal Weidmüller Sistemas de Interface S. A. Estrada Outeiro Polima, R. Augusto Dias da Silva, Lote B - Esc. 2 São Domingos de Rana 2785-515 Abóboda Tel. +351 214 459 191 Fax +351 214 455 871 weidmuller@weidmuller.pt www.weidmuller.pt	SY Syria Please contact Weidmüller Middle East FZE United Arab Emirates	VN Vietnam AUMI Industrial Equipment & Automation Company Limited E1, La Thanh Hotel 218 Doi Can Street District Hanoi City Tel. +84 4 37628601 Fax +84 4 62661391 aumi@aumi.com.vn www.aumi.com.vn Representative Office Weidmüller Pte. Ltd. Level 16 Saigon Tower Building 29 Le Duan Street District 1 Ho Chi Minh Tel. +848 3520 7717 Fax +848 3520 7604 info@weidmuller.com.sg
MK Macedonia Please contact our Representative Office Weidmüller Interface GmbH & Co. KG Serbia or ELEKTRO - SMK dool UL. III Makedonska brigada b.b. 1000 Skopje Tel. +389 22460295 Fax +389 22460298 Elektro-smk@telekabel.net.mk	NZ New Zealand Cuthbert S. Stewart Ltd. 27 Te Puni Street Petone PO Box 38496 Wellington Mail Centre 5054 Tel. (04) 568 6156 Fax (04) 568 6056 csl@cuthbertstewart.co.nz Cuthbert S. Stewart Ltd 4 Fred Thomas Drive Aon Building, Ground Floor, South Entry Takapuna PO Box 100 338 North Shore City 745 Tel. (09) 489 1751 Fax (09) 489 1752 cslak@cuthbertstewart.co.nz	PY Paraguay Please contact CPI SA Argentina	SZ Swaziland Please contact Phambili Interface South Africa	TH Thailand Pisanu Engineering Co. Ltd. Kwang Dingaeng, Khet Dingaeng 800/2 Soi Trakulsuk, Asoke- dindaeng Road Dindaeng, Bangkok 10400 Tel. +66 2 248 2896 Fax +66 2 642 9220 ecsales@pisanu.co.th www.pisanu.co.th Representative Office Weidmüller Pte. Ltd. 37/F, Sathorn Square Building 98 North Sathorn Road Bangkok, Silom Bangrak 10500 Tel. +66 2 105 6300 Fax +66 2 105 6301 info@weidmuller.com.sg
MT Malta E. S. S., Electrical Supplies & Services Ltd. San Gwakkim Road Mrieħel Tel. +356 21255777 Fax +356 21255999 robert.agius@ess.com.mt	OM Oman DAN INTERNATIONAL LLC. Ghala St. 111 BP 2901 Seeb Tel. +968 5036 77 Fax +968 5037 55 yedu@danintl.com	RO Romania Representative Office Weidmüller Interface GmbH & Co. KG Ionescu Crum Street, No. 1, 1st Tower, 1st Floor, Office 4 500446 Brasov - Brasov Business Park Tel. +40 (268) 446 222 Fax +40 (268) 446 224 claudiu.totea@weidmueller.com www.weidmueller.com	TR Turkey Weidmüller Elektronik Ticaret Ltd. Sirketi Kavacik Mah. Orhan Veli Kanik Caddesi 9/1 34810 Beykoz / Istanbul Tel. +90 (216) 537 10 70 Fax +90 (216) 537 10 77 info@weidmuller.com.tr www.weidmuller.com.tr	ZA South Africa Phambili Interface PO Box 193 1609 Johannesburg, Edenvale 5 Bundo Road, Sebenza 1610 Johannesburg Tel. +27 (11) 4521930 Fax +27 (11) 4526455 info@weidmuller.co.za www.weidmuller.co.za
MU Mauritius Mubelo Electrical Ltd. Office 26, Gateway building, St Jean Road Quatre Bornes Mauritius Tel. +230 4670989 Fax +230 4654051 richard.mubelo@orange.mu	PE Peru IMPEXINCA S.A.C. Calle Ortiz de Zevallos No. 105, Urb. San Antonio 18 Lima, Miraflores Tel. +51 1 447 5608 info@impexinca.pe www.impexinca.pe J & W CIA. S. A. Calle 6 Mz. D Lte. 23, Urb. Ind. Grimanesa 1 Callao Tel. +51 1 572 2539 Fax +51 1 572 0152 contacto@jwcia.com www.jwcia.com	RS Serbia Representative Office Weidmüller Interface GmbH & Co. KG Ustanicka 189, III sprat Iokal 7a 11050 Beograd Tel. +381 11 2885274 Fax +381 11 2885274 zoran.rabrenovic@ weidmueller.com	TN Tunisia Please contact Weidmüller E. U. R. L. France	ZM Zambia Please contact Phambili Interface South Africa
MW Malawi Please contact Phambili Interface South Africa	PH Philippines Enclosure Systems Specialists Inc. 2276 Don Chino Roces Avenue Extension Room 103/105 Narra Building 1231 Makati City Tel. +63 2 813 8580 Fax +63 2 813 8596 sales_encsys@pltdsl.net www.enclosuresystemsph.com	RU Russia OOO Weidmüller Warshavskoye highway, 25 A, bld. 6 Moskau 117105 Tel. +7 (495) 771-69-40 Fax +7 (495) 771-69-41 Info@weidmuller.ru www.weidmuller.ru	TW Taiwan Weidmüller (Hong Kong) Limited No. 3, Lane 89, ChungYang N. Rd. 24148 SanChuang City, Taipei Tel. +886 921 949 751 roy.lin@weidmueller.com.hk	ZW Zimbabwe Please contact Phambili Interface South Africa
MX Mexico W Interconnections S. A. DE C. V. Blvd. Hermanos Serdán 698, Col. San Rafael Oriente 72029 Puebla Tel. +52 (222) 268 6227 Fax +52 (222) 286 6242 clientes@weidmuller.com.mx		SA Saudi Arabia Please contact Weidmüller Middle East FZE United Arab Emirates	TZ Tanzania Please contact Phambili Interface South Africa	
MY Malaysia Connect Plus Technology Sdn Bhd No. 43, Jalan PJS 11/22, Bandar Sunway 46150 Petaling Jaya Selangor Darul Ehsan Tel. +60 3 5633 7363 Fax +60 3 5633 6562 paul@cptech.com.my www.cptech.com.my		SE Sweden Weidmüller AB Axel Danielssons väg 271 BOX 31025 SE-200 49 Malmö Tel. +46 77-143 00 44 Fax +46 40-37 48 60 info@weidmuller.se www.weidmuller.se		
		SG Singapore Weidmüller Pte. Ltd. 70 Bendemeer Road # 04-03 Luzerne Building Singapore 339940 Tel. +65 6841 5311 Fax +65 6841 5377 info@weidmuller.com.sg www.weidmuller.com.sg		

