



UNIT: mm




PIN ASSIGNMENT:



Electrical test:

- 1. 100% short, open, miswire test
- 2. Conduct resistance: $2\ \Omega$ (max)
- 3. Insulation resistance: $5\ M\Omega$ (min)
- 4. dielectric test: DC 300V



⑥	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK "MADE IN CHINA" + "10PCS"
⑤	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK "MADE IN CHINA" + "1PC"
④	TIE	2	WHITE L=100mm
③	OUT JACKET	12g	BEIGE (1V-29#) PVC-40P (MOULD NO: WM-40)
②	CABLE	1	BEIGE (1V-29#) USB2.0 UL2725 28#/1P+24#/2C+AEB OD: 4.7mm L=2000±10
①	CONN	2set	USB A MALE NICKEL PIN G/F 3PCS TYPE
NO.	NAME	Q'TY	SPECIFICATION

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN	Andy	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	101-1020-BE-00200
DECIDED		DATE	2013-8-23
VERSIONS/EDITION	A/0	PROJECTION	