




Field Interface Modules



Passive - 2 wire
16 Channel
Input Fused* w/LED
and Circuit Breaker
Allen-Bradley



Passive - 2 wire
16 Channel
Input
Allen-Bradley



Technical Data

Type	RS PLC DI W/ LD, F & CB		RS PLC 16PT DI 1 x 16	
Part number	996414	1771-ID16	995867	1746-IA16
Rated voltage	120 VAC		120 VAC	
Rated current	.25 A per channel / 12.0 A per module / 10 A circuit breaker		2.0 A per channel / 6.0 A per module / 3.0 A per common	
Cable connection	(1) 1 x 40 pin IDC		(1) 1 x 20 pin IDC	
LED Indicators	Yes		No	
Operating Temperature	0°C...+50°C		0°C...+50°C	
Storage Temperature	-20°C...+60°C		-20°C...+60°C	
Dimensions LxWxH mm	182 x 100 x 59		89 x 70 x 59	
Terminal Wire Size	#26...14 AWG		#26...14 AWG	
Terminal Type	Screw Clamp		Screw Clamp	
Approvals				

Wiring Schematics

