



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/9/04	
A		UPDATED	12/04/07	



SPECIFICATIONS:

Material:

Contact: Phosphor Bronze, 0.2mm thick

Plating: Tin over Copper underplate

Electrical:

Operating voltage: 250 VAC RMS max

Current rating: 20 Awg: 5 Amps max

22 Awg: 5 Amps max

24 Awg: 4 Amps max

26 Awg: 3 Amps max

28 Awg: 2 Amps max

30 Awg: 1 Amp max.

Contact resistance: 10 mohms max.

Dielectric withstanding voltage: 1500 VAC for 1 minute

Temperature rise: 30°C max.

Mechanical:

Wire size: 22 Awg thru 28 Awg

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.118" [3.0mm] CRIMP, MULTI ROW
HOUSINGS, TIN PLATED

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MM [INCHES] TOLERANCES: EXCEPT AS NOTED INCHES		HOLDS		DATE	
.X	± .10	ØX	± .10		
.XX	± .020	ØXX	± .015		
.XXX	± .015	ØXXX	± .010		
APPROVALS					
DRAWN	SS	9/9/04			
CHECKED					
APPROVED					

SIZE	PART NO.	REV.
X	DMT-C-F-T-1	A
REF:	SCALE: NTS	SHEET 1 OF 1