





SUGGESTED MTG. HOLE .228 DIA.

LEAD FINISH: SILVER	
BUSHING FINISH: SILVER	
CAPACITANCE	3000 pF MIN.
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C --- VDC MAX. 125°C 200 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	---
50	32
100	45
1 GHz	70
10 GHz	--



MARKING:

PART:
S1201054

BAG: SCI
1201-054

DATE CODE

QTY./BAG
(50 / BAG MAX.)

	6	5	4	3	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 SPECTRUM CONTROL INC.	ERIE, FAIRVIEW PENNSYLVANIA	
	CN 37798-ENG	CN 202986 REDRAWN	CN 199855	CN 185003 REDRAWN	CHANGE NOTICE	Fractions ± 1/64		Dwn. KRDZALIC	Description
						Dec. .xx±		Ckd. 10-15-07	FILTER, SING, Pi, BSHG
						Dec. .xxx± .010			
						Angles ±0° 30'			
						CODE IDENT. NO. DLSP2			
							Scale NONE		1201-054

