



LED Rechargeable Task Light Kit



Description

This LED rechargeable task light is suitable for both domestic and commercial tasks, especially in areas where there is no power. Supplied with both floor stand and tripod in a durable carry case, this task light is also cool to run and eliminates fire and burn hazards associated with halogen site lighting.

Features

- 2-3 hours work time
- 2-3 hours charge time
- 10W LED chip
- Includes AC and in car charger
- Supplied with floor stand and tripod
- Durable foam lined carry case
- Daylight (6000K) colour temperature

Range

LED Rechargeable Task Light Kit 7884612

Dimensions (mm)

	Height	Width	Depth
7884612 (on stand)	240	150	170

Technical Specification

Charger Input	230V AC or 12-24V DC
Charger Output	8.4V DC
Lamp Type	COB LED
Wattage	10W
Light Output	540lm
Lamp Col. Temp	6000K
IP Rating	IP65
Body Material	Die cast aluminium
Stand/Tripod Material	Steel

Standards

- BS EN 60598-1: 2008+A11: 2009
- BS EN 60598-2-4: 1997
- BS EN 62493: 2010
- BS EN 62471: 2009