


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -


ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
			D1	REVISED PER ECO-12-003798	29FEB12	DR



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
3/0 AWG SOLID OR STRANDED	3/0 AWG STRANDED	3/0 AWG SOLID OR STRANDED

- 1 STAMP AMP 3/0W* APPROX AS SHOWN
- 2 COPPER PER ASTM B-152, ANNEALED
- 3 0.00254 [.000100] MIN TIN PER ASTM B-545



327887

PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 76.3-96.3mm ² [150,000-190,000] SOLID OR STRANDED
TOOLING INFORMATION	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 18NOV94	TE Connectivity			
DIMENSIONS: INCHES		CHK DA PATTERSON 21NOV94				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD DA PATTERSON 21NOV94	NAME			
		PRODUCT SPEC	TERMINAL, RING TONGUE, FLAG, SOLISTRAND			
	FINISH	APPLICATION SPEC	SIZE			
		WEIGHT	A2 00779 C=327887			
MATERIAL		CUSTOMER DRAWING	SCALE	2:1	SHEET	1 of 1
					REV	D1