

NOTES:

1. ROHS COMPLIANT
2. MATERIAL:
PANEL CONNECTOR SOCKET - POLYPROPYLENE, UL RATING 94-HB
HEADER CONNECTOR - POLYESTER, UL RATING 94-V0
TERMINALS - PHOSPHOR BRONZE, TIN PLATED
WIRE - 24 AWG 1007/ 1569
3. MOUNTING: HOLE SIZE - 9/32" (7.14mm)
4. PANEL THICKNESS: .030" (.762mm) MIN - .250" (6.35mm) MAX
USE RNG 242 RETAINING RING WHEN ADDITIONAL SECURITY IS REQUIRED
5. LED LEAD LENGTH: 5mm FLANGELESS LED .250" (6.35mm)
6. U.S. & FOREIGN PATENT ISSUED AND PENDING

REVISIONS				
ECN #	REV	DESCRIPTION	DATE	INITIALS
	001	REVISED PER ECR 111009AZ01	11/26/10	KH

CABLE ORDERING CODE EXAMPLE:
CNX K E 4 1 12



TERMINATION *	
X =	STRIPPED END
E =	SINGLE ROW LOCKING HEADER
G =	SINGLE ROW PLAIN HEADER

WIRE SIZE *	
4	24 AWG

WIRE COLOR *	
1	WHITE - BLACK
2	RED - BLACK

WIRE LENGTH *	
04	4 INCHES (101.6mm)
06	6 INCHES (152.4mm)
08	8 INCHES (203.2mm)
12	12 INCHES (304.8mm)
18	18 INCHES (457.2mm)
24	24 INCHES (609.6mm)

* CALL FACTORY
FOR ADDITIONAL
OPTIONS



DIMENSION STYLE: INCHES / MM GENERAL TOLERANCES UNLESS OTHERWISE SPECIFIED: INCHES ±.500 MM ± 12.7  THIRD ANGLE PROJECTION	MATERIAL	VCC OPTOELECTRONICS 190 BOSSTICK BLVD. SUITE 101 SAN MARCOS, CA 92069 U.S.A PHONE: (760) 560-1300, FAX: (760) 560-1301 EMAIL: vccsales@vccite.com			
	SEE NOTES	TITLE:			
PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF VISUAL COMMUNICATIONS COMPANY, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF VISUAL COMMUNICATIONS COMPANY, INC. IS PROHIBITED.	FINISH	CNX K CABLE ASSEMBLY			
	SEE NOTES				
	APPROVAL	DATE	SIZE	DWG. NO.	REV
	DRAWN K.Howard	11/26/10	B	CNX K ASSY	001
	CHECKED DPZ	11/29/10	SCALE: 1:1		SHEET 1 OF 1
DO NOT SCALE DRAWING					