

Bi-Color and Bi-Polar LEDs

Shape	Part Number	Emitting Color	Emitting Material	Lens-Color	Wave Length (nm)	Luminous Intensity IF=20mA(mcd) Min. Max.		Viewing Angle	Figure No.
3mm Round	LUGR29M	Red	GaAsP/GaP	White Diffused	625	12.5 - 50		60°	1
		Green	GaP		565	12.5 - 50			
	LUYR29M	Red	GaAsP/GaP	White Diffused	625	12.5 - 50		60°	
		Yellow	GaAsP/GaP		590	12.5 - 50			
	LUGY29M	Green	GaP	White Diffused	565	12.5 - 50		60°	
		Yellow	GaAsP/GaP		590	12.5 - 50			
3mm Round	LUGR34M	Red	GaAsP/GaP	White Diffused	625	12.5 - 50		60°	2
		Green	GaP		565	12.5 - 50			
	LMRMG34M-CC	Red	GaAlAs	White Diffused	660	90 - 300		60°	
		Green	GaP		565	12.5 - 50			
3mm Round	LUGR37M	Red	GaAsP/GaP	White Diffused	625	8 - 40		60°	3
		Green	GaP		565	8 - 40			
	LUYR37M	Red	GaAsP/GaP	White Diffused	625	8 - 40		60°	
		Yellow	GaAsP/GaP		590	5 - 20			
	LUGY37M	Green	GaP	White Diffused	565	8 - 40		60°	
		Yellow	GaAsP/GaP		590	5 - 20			
	LURR37D	Red	GaAsP/GaP	Red Diffused	625	8 - 40		60°	
		Red	GaAsP/GaP		625	8 - 40			
	LUGG37D	Green	GaP	Green Diffused	565	5 - 20		60°	
		Green	GaP		565	5 - 20			
	LUYY37D	Yellow	GaAsP/GaP	Yellow Diffused	590	5 - 20		60°	
		Yellow	GaAsP/GaP		590	5 - 20			

