




	20	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	
M	SHEET DESCRIPTION CONFIGURATIONS																				M
L																					L
K																					K
J																					J
I																					I
H																					H
G																					G
F																					F
E	2X6 - STANDARD (STD)																				E
D																					D
C	2X8 - STANDARD (STD)																				C
B																					B
A	2X10 - STANDARD (STD)																				A
	1b_frame_A1_P_AM_T Rev. G 2012/01/11	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	

ENTER DESCRIPTION		DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
EC NO: UAU2015-0456						MM ONLY		1.5:1	METRIC		
DRAWN: APROFIT				mm INCH		DRAWN BY DATE		TITLE			
CHKD: KBORUSZEWSKI						CHECKED BY DATE					
APPR: VKOSHY				4 PLACES ± --- ± ---		APPROFIT 2014/04/28				MX150 BLADE	
				3 PLACES ± --- ± ---						DUAL ROW SEALED ASSEMBLY	
				2 PLACES ± 0.10 ± ---		KBORUSZEWSKI 2014/04/29				MAT SEAL	
				1 PLACE ± 0.2 ± ---		APPROVED BY DATE				molex	
				0 PLACE ± --- ± ---		VKOSHY 2014/05/14					
				ANGULAR ± 1 °		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE NOTE 2a.		SD-33482-0001		2 OF 9	
						SIZE A1		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

1b_frame_A1_P_AM_T
Rev. G 2012/01/11



ENTER DESCRIPTION EC NO: UAU2015-0456 DRAWN BY: APROFFITT 2014/09/24 CHECKED BY: CHYKOBORUSZEWSKI 2014/09/24 APPR: WKOSHY 2014/09/25										REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
															MM ONLY		3:1	METRIC		
													▽=0 ▽=0 ▽=0	4 PLACES	± ---	± ---	DRAWN BY	DATE	TITLE	MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL
															± ---	± ---	APPROFFITT	2014/04/28		
															± ---	± ---	CHECKED BY	DATE		
															± 0.10	± ---	KBORUSZEWSKI	2014/04/29		
															± 0.2	± ---	APPROVED BY	DATE		
± ---	± ---	VKOSHY	2014/05/14	DOCUMENT NO.	SD-33482-0001	SHEET NO. 4 OF 9														
ANGULAR ± 1 °	MATERIAL NO.	SEE NOTE 2a.																		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE A1	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		

1b_frame_A1_P_AM.T Rev. G 2012/01/11	19	18	17	16	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1
---	----	----	----	----	----	----	----	----	----	----	---	---	---	---	---	---	---	---	---








SHEET DESCRIPTION

BLADE SEALED ASSEMBLY


CHARTED DIMENSIONS

DESCRIPTION	DIMENSIONS				
	A	B	C	D	E
2X6	29.54	1.75	32.27	54.45	22.23
2X8	36.54	1.75	38.88	54.45	22.23
2X10	43.64	1.75	45.65	54.45	22.05

OPTIONAL LASER MARKING ON
THIS SURFACE SEE NOTE 3g.



PRIMARY LOCK REINFORCEMENT (PLR) SHOWN
IN PRE-STAGED POSITION
SECTION W-W





PRIMARY LOCK REINFORCEMENT (PLR) SHOWN
IN FINAL-LOCK POSITION
SECTION V-V

ENTER DESCRIPTION LEC NO: UAU2015-0456 DRAWN BY: ITT 2014/09/24 CHKD BY: KBORUSZEWSKI 2014/09/24 APPR: VKOSHY 2014/09/25		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 3:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
					DRAWN BY APPROFIT	DATE 2014/04/28	MX150 BLADE					
					CHECKED BY KBORUSZEWSKI	DATE 2014/04/29	DUAL ROW SEALED ASSEMBLY					
					APPROVED BY VKOSHY	DATE 2014/05/14	MAT SEAL					
								molex				
					ANGULAR ± 1°		MATERIAL NO.	DOCUMENT NO.	SHEET NO.			
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE NOTE 2a.		SD-33482-0001 5 OF 9			
					SIZE 1	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

SHEET DESCRIPTION
SYSTEM PACKAGING

CHARTED DIMENSIONS				
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS	
			K	L
2X6	STANDARD	STANDARD	72.79	35.58
2X8	STANDARD	STANDARD	72.67	42.25
2X10	STANDARD	STANDARD	72.78	49.05



ENTER DESCRIPTION EC NO: UA02015-0456 DRAWN BY: APPROFFITT 2014/09/22 CHKOBORUSZEWSKI 2014/09/24 APPR: MOXST 2014/09/25	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION	TITLE MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL molex	DOCUMENT NO. SD-33482-0001	SHEET NO. 6 OF 9
					MM ONLY		4:1	METRIC				
					DRAWN BY	DATE	TITLE					
			4 PLACES ± --- ± ---		APPROFIT	2014/04/28						
			3 PLACES ± --- ± ---		CHECKED BY	DATE						
			2 PLACES ± 0.10 ± ---		KBORUSZEWSKI	2014/04/29						
			1 PLACE ± 0.2 ± ---		APPROVED BY	DATE						
			0 PLACE ± --- ± ---		VKOSHY	2014/05/14						
					MATERIAL NO.							
					SEE NOTE 2a.							
					SIZE							
		A1										
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										

SHEET DESCRIPTION



BACKSHELL NOTES

BACKSHELL NOTES: VALID UNLESS OTHERWISE SPECIFIED

1. GENERAL:
- a. APPLICATION SPECIFICATION SEE: AS-34951-001
- DESIGNED TO MATE WITH BLADE SEALED ASSEMBLY
 - SPECIFIED IN MOLEX DRAWING SD-33482-0001.
 - SYSTEM TO BE USED WITH WIRE WITHIN DIAMETER RANGE OF 1.2mm TO 2.69mm.
 - COMPONENTS ARE OPTIONAL AND MUST BE PURCHASED SEPERATELY.
 - BACKSHELL DESIGN IS OWNED BY SCHLEMMER.
 - FOR ADDITIONAL INFORMATION SEE THE BACKSHELL COMPONENT DRAWING SD-34950-0001.

BACKSHELL CUSTOMER
MODEL NUMBER LEGEND


- 34950-XXXX
- CUSTOMER MODEL COMPONENTS
 - 0 - BACKSHELL ONLY
 - 1 - BACKSHELL & MX150 HOUSING KEY A ASSEMBLY
 - 2 - BACKSHELL & MX150 HOUSING KEY B ASSEMBLY
 - 3 - BACKSHELL & MX150 HOUSING KEY C ASSEMBLY
 - 4 - BACKSHELL & MX150 HOUSING KEY D ASSEMBLY
 - BACKSHELL FEATURES
 - 1 - WITH RIBS
 - 2 - WITHOUT RIBS
 - MX150 CIRCUIT SIZE 04, 06, 08, 12, 16, 20



ENTER DESCRIPTION EC NO: UAU2015-0456 DRAWN BY: TTT 2014/09/22 CHKD: KBORUSZEWSKI 2014/09/24 APPR: WKOSHY 2014/09/25		QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
			mm		INCH		DRAWN BY DATE APPROFIT 2014/04/28		TITLE MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL		
				4 PLACES	± .000	± .000	CHECKED BY DATE KBORUSZEWSKI 2014/04/29		molex SD-33482-0001		
				3 PLACES	± .005	± .005	APPROVED BY DATE VKOSHY 2014/05/14				
				2 PLACES	± 0.10	± .004	MATERIAL NO.				
C	REV		1 PLACE	± 0.2	± .008	SEE NOTE 2a.		DOCUMENT NO.		SHEET NO.	
			0 PLACE	± .000	± .000	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SD-33482-0001		7 OF 9	
		ANGULAR ± 1 °		SIZE A 1		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

SHEET DESCRIPTION

BACKSHELL





ENTER DESCRIPTION EC NO: UA02015-0456 DRAWN BY: APPOFFITT 2014/09/22 CHKD BY: KBORUSZEWSKI 2014/09/24 APPR BY: WKOSHY 2014/09/25	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 3.5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
					DRAWN BY DATE		TITLE		
			4 PLACES ± --- ± ---		APPOFFITT 2014/04/28		MX150 BLADE		
			3 PLACES ± --- ± ---		CHECKED BY DATE		DUAL ROW SEALED ASSEMBLY		
			2 PLACES ± 0.10 ± ---		KBORUSZEWSKI 2014/04/29		MAT SEAL		
			1 PLACE ± 0.2 ± ---		APPROVED BY DATE		molex		
			0 PLACE ± --- ± ---		WKOSHY 2014/05/14				
			ANGULAR ± 1 °		MATERIAL NO.		DOCUMENT NO.		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE NOTE 2a.		SD-33482-0001		
REV			SIZE		SHEET NO.				
			A1		8 OF 9				

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



SHEET DESCRIPTION

BACKSHELL CONFIGURATIONS



CHARTED DIMENSIONS							
CKT	BLADE CONFIGURATION	RECEPTACLE CONFIGURATION	DIMENSIONS				
			M	N	P	R	S
2X6	STANDARD	STANDARD	106.83	37.84	37.27	35.83	36.83





OVERALL MATED SYSTEM WITH BLADE AND RECEPTACLE BACKSHELL



OVERALL MATED SYSTEM WITH BLADE BACKSHELL



OVERALL MATED SYSTEM WITH RECEPTACLE BACKSHELL



BLADE SEALED ASSEMBLY WITH BLADE BACKSHELL

ENTER DESCRIPTION EC NO: UAU2015-0456 DRAWN: APROFFITT 2014/09/22 CHKD: KBORUSZEWSKI 2014/09/24 APPR: VKOSHY 2014/09/25	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	TITLE MX150 BLADE DUAL ROW SEALED ASSEMBLY MAT SEAL molex DOCUMENT NO. SD-33482-0001 SHEET NO. 9 OF 9	
					DRAWN BY DATE						
					CHECKED BY DATE						
					APPROVED BY DATE						
					MATERIAL NO.		DOCUMENT NO.				
	REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	mm		INCH		APPROFFITT 2014/04/28			
				4 PLACES ± --- ± ---		3 PLACES ± --- ± ---		KBORUSZEWSKI 2014/04/29			
				2 PLACES ± 0.10 ± ---		1 PLACE ± 0.2 ± ---		VKOSHY 2014/05/14			
				0 PLACE ± --- ± ---		ANGULAR ± 1 °		SEE NOTE 2a.			
						SIZE A1		INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

MAT SEAL

CONNECTOR HOUSING

GROMMET CAP

PRIMARY LOCK REINFORCEMENT (PLR)

TERMINAL POSITION 6

TERMINAL POSITION 1

TERMINAL POSITION 12

TERMINAL POSITION 7

ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
A-YL	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE

FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS												STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION														BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12				
KEY A, BLACK	33482-1201	A-BLK	GCP	PLR	M													SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1202	B-LG	GCP	PLR	M													SALEABLE		34950-1210	34950-1220
KEY C, BROWN	33482-1203	C-BR	GCP	PLR	M													NOT RECOMMENDED	SEE 33482-1261	34950-1210	34950-1220
KEY D, GREEN	33482-1204	D-GR	GCP	PLR	M													NOT RECOMMENDED	SEE 33482-1262	34950-1210	34950-1220
VOID KEY	33482-1205																				
KEY A, BLACK	33482-1206	A-BLK	GCP	PLR	M						6							SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1207	B-LG	GCP	PLR	M						6							SALEABLE		34950-1210	34950-1220
KEY C, BROWN	33482-1208	C-BR	GCP	PLR	M						6							NOT RECOMMENDED		34950-1210	34950-1220
KEY D, GREEN	33482-1209	D-GR	GCP	PLR	M						6							NOT RECOMMENDED		34950-1210	34950-1220
VOID KEY	33482-1210																				
KEY A, BLACK	33482-1211	A-BLK	GCP	PLR	M						6	7						SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1212	B-LG	GCP	PLR	M						6	7						SALEABLE		34950-1210	34950-1220
KEY C, BROWN	33482-1213	C-BR	GCP	PLR	M						6	7						NOT RECOMMENDED		34950-1210	34950-1220
KEY D, GREEN	33482-1214	D-GR	GCP	PLR	M						6	7						NOT RECOMMENDED		34950-1210	34950-1220
VOID KEY	33482-1215																				
KEY A, BLACK	33482-1216	A-BLK	GCP	PLR	M	1					6	7						SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1217	B-LG	GCP	PLR	M	1					6	7						SALEABLE		34950-1210	34950-1220
KEY C, BROWN	33482-1218	C-BR	GCP	PLR	M	1					6	7						NOT RECOMMENDED	SEE 33482-1320	34950-1210	34950-1220
KEY D, GREEN	33482-1219	D-GR	GCP	PLR	M	1					6	7						NOT RECOMMENDED	SEE 33482-1285	34950-1210	34950-1220
VOID KEY	33482-1220																				
KEY A, BLACK	33482-1221	A-BLK	GCP	PLR	M	1					6	7					12	SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1222	B-LG	GCP	PLR	M	1					6	7					12	SALEABLE		34950-1210	34950-1220
KEY C, BROWN	33482-1223	C-BR	GCP	PLR	M	1					6	7					12	NOT RECOMMENDED		34950-1210	34950-1220
KEY D, GREEN	33482-1224	D-GR	GCP	PLR	M	1					6	7					12	NOT RECOMMENDED		34950-1210	34950-1220
VOID KEY	33482-1225																				
KEY A, BLACK	33482-1226	A-BLK	GCP	PLR	M						6						12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1227	A-BLK	GCP	PLR	M	1	2	3	4	5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1228	B-LG	GCP	PLR	M	1	2	3	4	5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY C, BROWN	33482-1229	C-BR	GCP	PLR	M	1	2	3	4	5	6	7	8	9	10	11	12	NOT RECOMMENDED	SEE 33482-1263	34950-1210	34950-1220
KEY D, GREEN	33482-1230	D-GR	GCP	PLR	M	1	2	3	4	5	6	7	8	9	10	11	12	NOT RECOMMENDED	SEE 33482-1264	34950-1210	34950-1220
VOID KEY	33482-1231																				
KEY A, BLACK	33482-1232	A-BLK	GCP	PLR	M		2	3					8			11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1233	A-BLK	GCP	PLR	M		2	3		5	6	7	8			11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1234	A-BLK	GCP	PLR	M						6	7						SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1235	A-BLK	GCP	PLR	M		2	3			6	7	8		10	11		SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1236	B-LG	GCP	PLR	M	1				5	6	7	8	9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1237	A-BLK	GCP	PLR	M		2											SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1238	B-LG	GCP	PLR	M		2							9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1239	A-BLK	GCP	PLR	M	1				5	6	7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1240	A-BLK	GCP	PLR	M		2	3					8	9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1241	A-BLK	GCP	PLR	M							7	8	9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1242	A-BLK	GCP	PLR	M							7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1243	A-BLK	GCP	PLR	M		2							9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1244	A-BLK	GCP	PLR	M		2		4									SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1245	A-BLK	GCP	PLR	M									9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1246	A-BLK	GCP	PLR	M											11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1247	A-BLK	GCP	PLR	M		2	3	4			7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1248	A-BLK	GCP	PLR	M	1		3	4	5	6	7	8					SALEABLE		34950-1210	34950-1220



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET


KEY A, BLACK	33482-1249	A-BLK	GCP	PLR	M									10	11	12	SALEABLE		34950-1210	34950-1220		
KEY A, BLACK	33482-1250	A-BLK	GCP	PLR	M				4	5	6	7	8	9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1251	A-BLK	GCP	PLR	M		2		4	5			8		10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1252	A-BLK	GCP	PLR	M							7						SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1253	A-BLK	GCP	PLR	M		2	3	4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1254	A-BLK	GCP	PLR	M		2	3	4	5					10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1255	A-BLK	GCP	PLR	M		2	3	4	5	6	7			10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1256	A-BLK	GCP	PLR	M	1					6	7		9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1257	A-BLK	GCP	PLR	M									9	10		12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1258	A-BLK	GCP	PLR	M		2	3								11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1259	A-BLK	GCP	PLR	M	1	2	3	4	5				9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1260	A-BLK	GCP	PLR	M											11	12	SALEABLE		34950-1210	34950-1220	
KEY C, DARK GRAY	33482-1261	C-DG	GCP	PLR	M													SALEABLE		34950-1210	34950-1220	
KEY D, STONE GRAY	33482-1262	D-SG	GCP	PLR	M													SALEABLE		34950-1210	34950-1220	
KEY C, DARK GRAY	33482-1263	C-DG	GCP	PLR	M	1	2	3	4	5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY D, STONE GRAY	33482-1264	D-SG	GCP	PLR	M	1	2	3	4	5	6	7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1265	A-BLK	GCP	PLR	M				3	4	5	6	7	8	9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1266	A-BLK	GCP	PLR	M	1	2	3	4	5	6	7					12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1267	A-BLK	GCP	PLR	M				3	4	5	6	7					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1268	A-BLK	GCP	PLR	M				3	4	5	6	7	8	9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1269	A-BLK	GCP	PLR	M	1	2	3	4	5			8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1270	A-BLK	GCP	PLR	M		2		4			7	8	9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1271	A-BLK	GCP	PLR	M		2					7	8	9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1272	A-BLK	GCP	PLR	M		2					7	8	9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1273	A-BLK	GCP	PLR	M								8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1274	A-BLK	GCP	PLR	M	1			3	4	5	6		8		10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1275	A-BLK	GCP	PLR	M					4				8		10		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1276	A-BLK	GCP	PLR	M	1	2	3	4		6			8		10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1277	A-BLK	GCP	PLR	M	1	2	3								11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1278	A-BLK	GCP	PLR	M						6						12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1279	A-BLK	GCP	PLR	M	1	2	3	4	5		7	8	9	10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1280	A-BLK	GCP	PLR	M	1	2	3	4	5	6			9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1281	A-BLK	GCP	PLR	M		2		4		6		8		10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1282	A-BLK	GCP	PLR	M	1	2	3	4	5	6			9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1283	A-BLK	GCP	PLR	M						6			9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1284	A-BLK	GCP	PLR	M	1			3	4	5	6	7	8		10	11	12	SALEABLE		34950-1210	34950-1220
KEY D, STONE GRAY	33482-1285	D-SG	GCP	PLR	M	1					6	7						SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1286	A-BLK	GCP	PLR	M		2	3					8	9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1287	A-BLK	GCP	PLR	M	1						7						SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1288	A-BLK	GCP	PLR	M	1					6							SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1289	A-BLK	GCP	PLR	M	1	2	3	4	5	6		8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1290	A-BLK	GCP	PLR	M	1						7					12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1291	A-BLK	GCP	PLR	M	1	2	3	4	5	6	7	8				12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1292	A-BLK	GCP	PLR	M									9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1293	A-BLK	GCP	PLR	M				3	4				9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1294	A-BLK	GCP	PLR	M	1	2			5	6	7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1295	A-BLK	GCP	PLR	M	1	2			5	6	7	8			11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1296	A-BLK	GCP	PLR	M	1	2	3	4	5	6	7	8	9	10			SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1297	A-BLK	GCP	PLR	M				4		6				10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1298	A-BLK	GCP	PLR	M						6					11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1299	A-BLK	GCP	PLR	M	1	2					7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1300	A-BLK	GCP	PLR	M	1	2	3					8		10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1301	A-BLK	GCP	PLR	M	1	2					7	8				12	SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-1302	B-LG	GCP	PLR	M										10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1303	A-BLK	GCP	PLR	M	1	2	3	4			7	8	9	10		12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1304	A-BLK	GCP	PLR	M	1	2	3	4			7	8	9	10			SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-1305	B-LG	GCP	PLR	M										10	11	12	SALEABLE		34950-1210	34950-1220	
KEY B, LIGHT GRAY	33482-1306	B-LG	GCP	PLR	M	1	2	3	4	5	6	7			10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1307	A-BLK	GCP	PLR	M	1	2	3	4	5		7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1308	A-BLK	GCP	PLR	M							7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1309	A-BLK	GCP	PLR	M	1							8		10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1310	A-BLK	GCP	PLR	M	1			4							11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1311	A-BLK	GCP	PLR	M	1	2		4	5	6	7		9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1312	A-BLK	GCP	PLR	M								8	9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1313	A-BLK	GCP	PLR	M				3	4	5	6		8	9	10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1314	A-BLK	GCP	PLR	M				3			6	7	8	9	10		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1315	A-BLK	GCP	PLR	M						6	7	8	9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1316	A-BLK	GCP	PLR	M					5	6	7	8			11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1317	A-BLK	GCP	PLR	M	1	2											SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1318	A-BLK	GCP	PLR	M	1	2	3	4	5	6	7	8					SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1319	A-BLK	GCP	PLR	M	1	2	3	4	5	6	7	8	9				SALEABLE		34950-1210	34950-1220	
KEY C, DARK GRAY	33482-1320	C-DG	GCP	PLR	M	1					6	7						SALEABLE		34950-1210	34950-1220	
KEY C, BROWN	33482-1321	C-BR	GCP	PLR	M	1	2	3	4	5	6							NOT RECOMMENDED	SEE 33482-1328	34950-1210	34950-1220	
KEY C, BROWN	33482-1322	C-BR	GCP	PLR	M	1	2			5	6							NOT RECOMMENDED	SEE 33482-1329	34950-1210	34950-1220	
KEY A, BLACK	33482-1323	A-BLK	GCP	PLR	M				3			7		9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1324	A-BLK	GCP	PLR	M				3					9	10	11	12	SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1325	A-BLK	GCP	PLR	M				3					9				SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1326	A-BLK	GCP	PLR	M					5	6	7			10	11		SALEABLE		34950-1210	34950-1220	
KEY A, BLACK	33482-1327	A-BLK	GCP	PLR	M																	



MX150 2X6 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

KEY C, DARK GRAY	33482-1329	C-DG	GCP	PLR	M	1	2			5	6							SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1330	A-BLK	GCP	PLR	M	1	2	3	4					9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1331	A-BLK	GCP	PLR	M	1	2				6	7	8				12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1332	A-BLK	GCP	PLR	M				4	5		7	8	9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1333	A-BLK	GCP	PLR	M				4					9	10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1334	A-BLK	GCP	PLR	M				4	5			8		10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1335	A-BLK	GCP	PLR	M	1	2		4	5	6	7					12	SALEABLE		34950-1210	34950-1220
KEY A, YELLOW	33482-1336	A-YL	GCP	PLR	M													SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1337	B-LG	GCP	PLR	M					5			8					SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1338	B-LG	GCP	PLR	M					5			8			11	12	SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1339	B-LG	GCP	PLR	M			3	4	5			8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1340	B-LG	GCP	PLR	M	1	2	3	4	5			8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1341	A-BLK	GCP	PLR	M	1	2	3		5				9		11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1342	A-BLK	GCP	PLR	M		2	3		5						11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1343	A-BLK	GCP	PLR	M	1	2	3						9		11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1344	A-BLK	GCP	PLR	M	1	2	3	4	5				9		11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1345	A-BLK	GCP	PLR	M		2	3	4	5						11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1346	A-BLK	GCP	PLR	M	1												SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1347	A-BLK	GCP	PLR	M	1	2	3										SALEABLE		34950-1210	34950-1220
KEY B, LIGHT GRAY	33482-1348	B-LG	GCP	PLR	M	1	2	3	4		6					11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1349	A-BLK	GCP	PLR	M				4			7	8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1350	A-BLK	GCP	PLR	M		2						8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1351	A-BLK	GCP	PLR	M		2		4				8		10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1352	A-BLK	GCP	PLR	M	1	2	3	4	5	6		8		10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1353	A-BLK	GCP	PLR	M	1					6	7	8				12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1354	A-BLK	GCP	PLR	M		2	3	4		6		8		10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1355	A-BLK	GCP	PLR	M		2				6	7	8		10	11		SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1356	A-BLK	GCP	PLR	M	1	2	3	4		6				10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1357	A-BLK	GCP	PLR	M					5			8					SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1358	A-BLK	GCP	PLR	M				4						10			SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1359	A-BLK	GCP	PLR	M				4			7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1360	A-BLK	GCP	PLR	M					5	6		8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1361	A-BLK	GCP	PLR	M				4	5	6		8	9	10	11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1362	A-BLK	GCP	PLR	M	1	2	3		5	6	7	8	9		11	12	SALEABLE		34950-1210	34950-1220
KEY A, BLACK	33482-1363	A-BLK	GCP	PLR	M				4	5		7	8	9	10	11	12	SALEABLE		34950-1210	34950-1220

MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET



FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
A-YW	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY		
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16					
KEY A, BLACK	33482-1601	A-BLK	GCP	PLR	M																	SALEABLE				
KEY B, LIGHT GRAY	33482-1602	B-LG	GCP	PLR	M																	SALEABLE				
KEY C, BROWN	33482-1603	C-BR	GCP	PLR	M																	NOT RECOMMENDED	SEE 33482-1725			
KEY D, GREEN	33482-1604	D-GR	GCP	PLR	M																	NOT RECOMMENDED	SEE 33482-1726			
VOID KEY	33482-1605																									
KEY A, BLACK	33482-1606	A-BLK	GCP	PLR	M								8									SALEABLE				
KEY B, LIGHT GRAY	33482-1607	B-LG	GCP	PLR	M								8									SALEABLE				
KEY C, BROWN	33482-1608	C-BR	GCP	PLR	M								8									NOT RECOMMENDED	SEE 33482-1751			
KEY D, GREEN	33482-1609	D-GR	GCP	PLR	M								8									NOT RECOMMENDED	SEE 33482-1752			
VOID KEY	33482-1610												8													
KEY A, BLACK	33482-1611	A-BLK	GCP	PLR	M								8	9								SALEABLE				
KEY B, LIGHT GRAY	33482-1612	B-LG	GCP	PLR	M								8	9								SALEABLE				
KEY C, BROWN	33482-1613	C-BR	GCP	PLR	M								8	9								NOT RECOMMENDED	SEE 33482-1753			
KEY D, GREEN	33482-1614	D-GR	GCP	PLR	M								8	9								NOT RECOMMENDED	SEE 33482-1754			
VOID KEY	33482-1615												8	9												
KEY A, BLACK	33482-1616	A-BLK	GCP	PLR	M	1							8	9								SALEABLE				
KEY B, LIGHT GRAY	33482-1617	B-LG	GCP	PLR	M	1							8	9								SALEABLE				
KEY C, BROWN	33482-1618	C-BR	GCP	PLR	M	1							8	9								NOT RECOMMENDED	SEE 33482-1755			
KEY D, GREEN	33482-1619	D-GR	GCP	PLR	M	1							8	9								NOT RECOMMENDED	SEE 33482-1756			
VOID KEY	33482-1620					1							8	9												
KEY A, BLACK	33482-1621	A-BLK	GCP	PLR	M	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	SALEABLE				
KEY B, LIGHT GRAY	33482-1622	B-LG	GCP	PLR	M	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	SALEABLE				
KEY C, BROWN	33482-1623	C-BR	GCP	PLR	M	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	NOT RECOMMENDED	SEE 33482-1727			
KEY D, GREEN	33482-1624	D-GR	GCP	PLR	M	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	NOT RECOMMENDED	SEE 33482-1728			
VOID KEY	33482-1625					1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16					
KEY A, BLACK	33482-1626	A-BLK	GCP	PLR	M															15		SALEABLE				
KEY A, BLACK	33482-1627	A-BLK	GCP	PLR	M	1							8	9							16	SALEABLE				
KEY B, LIGHT GRAY	33482-1628	B-LG	GCP	PLR	M	1							8	9							16	SALEABLE				
KEY C, BROWN	33482-1629	C-BR	GCP	PLR	M	1							8	9							16	NOT RECOMMENDED	SEE 33482-1757			
KEY D, GREEN	33482-1630	D-GR	GCP	PLR	M	1							8	9							16	NOT RECOMMENDED	SEE 33482-1758			
VOID KEY	33482-1631					1							8	9							16					
KEY A, BLACK	33482-1632	A-BLK	GCP	PLR	M				4			7	8				12	13	14			SALEABLE				
KEY A, BLACK	33482-1633	A-BLK	GCP	PLR	M			3	4	5					10	11	12	13	14	15	16	SALEABLE				
KEY A, BLACK	33482-1634	A-BLK	GCP	PLR	M							7	8				12	13	14			SALEABLE				
KEY B, LIGHT GRAY	33482-1635	B-LG	GCP	PLR	M								8					13	14	15	16	SALEABLE				
KEY A, BLACK	33482-1636	A-BLK	GCP	PLR	M										10	11		13	14	15	16	SALEABLE				
KEY A, BLACK	33482-1637	A-BLK	GCP	PLR	M										10	11				15	16	SALEABLE				
KEY A, BLACK	33482-1638	A-BLK	GCP	PLR	M								8	9	10	11	12				15	16	SALEABLE			
KEY A, BLACK	33482-1639	A-BLK	GCP	PLR	M															15		SALEABLE				
KEY A, BLACK	33482-1640	A-BLK	GCP	PLR	M					5											16	SALEABLE				
KEY A, BLACK	33482-1641	A-BLK	GCP	PLR	M					5												SALEABLE				
KEY B, LIGHT GRAY	33482-1642	B-LG	GCP	PLR	M				4		6	7	8				12		14			SALEABLE				
KEY A, BLACK	33482-1643	A-BLK	GCP	PLR	M															15	16	SALEABLE				
KEY B, LIGHT GRAY	33482-1644	B-LG	GCP	PLR	M				4													SALEABLE				
KEY B, LIGHT GRAY	33482-1645	B-LG	GCP	PLR	M				4		6	7	8									SALEABLE				
KEY A, BLACK	33482-1646	A-BLK	GCP	PLR	M				4		6	7	8				12					SALEABLE				
KEY A, BLACK	33482-1647	A-BLK	GCP	PLR	M																16	SALEABLE				
KEY A, BLACK	33482-1648	A-BLK	GCP	PLR	M				4								12					SALEABLE				
KEY B, LIGHT GRAY	33482-1649	B-LG	GCP	PLR	M																16	SALEABLE				
KEY B, LIGHT GRAY	33482-1650	B-LG	GCP	PLR	M				4								12		14			SALEABLE				
KEY B, LIGHT GRAY	33482-1651	B-LG	GCP	PLR	M														14			SALEABLE				
KEY B, LIGHT GRAY	33482-1652	B-LG	GCP	PLR	M						6	7	8						14			SALEABLE				
KEY A, BLACK	33482-1653	A-BLK	GCP	PLR	M									9						15		SALEABLE				
KEY A, BLACK	33482-1654	A-BLK	GCP	PLR	M				4				8				12					SALEABLE				
KEY B, LIGHT GRAY	33482-1655	B-LG	GCP	PLR	M				4				8				12		14			SALEABLE				
KEY B, LIGHT GRAY	33482-1656	B-LG	GCP	PLR	M								8						14			SALEABLE				
KEY A, BLACK	33482-1657	A-BLK	GCP	PLR	M	1						7										SALEABLE				
KEY B, LIGHT GRAY	33482-1658	B-LG	GCP	PLR	M				4		6	7	8				12		14			SALEABLE				
KEY B, LIGHT GRAY	33482-1659	B-LG	GCP	PLR	M				2			6	7	8						14		SALEABLE				
KEY B, LIGHT GRAY	33482-1660	B-LG	GCP	PLR	M				2				8						14			SALEABLE				

MX150 2X8 BLADE SEALED ASSY MAT SEAL BOM AND PIN OUT SHEET


[illegible]



MX150 2X8 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY			
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																		BACKSHELL WITH RIBS		BACKSHELL WITHOUT RIBS	
HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16								
KEY A, BLACK	33482-1748	A-BLK	GCP	PLR	M		2					9			12	13	14		16	SALEABLE							
KEY A, BLACK	33482-1749	A-BLK	GCP	PLR	M	1							10	11	12	13	14		16	SALEABLE							
KEY A, BLACK	33482-1750	A-BLK	GCP	PLR	M	1	2					9	10	11	12	13	14		16	SALEABLE							
KEY C, DARK GRAY	33482-1751	C-DG	GCP	PLR	M						8									SALEABLE							
KEY D, STONE GRAY	33482-1752	D-SG	GCP	PLR	M						8									SALEABLE							
KEY C, DARK GRAY	33482-1753	C-DG	GCP	PLR	M						8	9								SALEABLE							
KEY D, STONE GRAY	33482-1754	D-SG	GCP	PLR	M						8	9								SALEABLE							
KEY C, DARK GRAY	33482-1755	C-DG	GCP	PLR	M	1					8	9								SALEABLE							
KEY D, STONE GRAY	33482-1756	D-SG	GCP	PLR	M	1					8	9								SALEABLE							
KEY C, DARK GRAY	33482-1757	C-DG	GCP	PLR	M	1					8	9							16	SALEABLE							
KEY D, STONE GRAY	33482-1758	D-SG	GCP	PLR	M	1					8	9							16	SALEABLE							
KEY A, BLACK	33482-1759	A-BLK	GCP	PLR	M	1	2	3	4	5		8	9	10	11	12	13	14	16	SALEABLE							
KEY A, BLACK	33482-1760	A-BLK	GCP	PLR	M		2					7	9						16	SALEABLE							
KEY A, BLACK	33482-1761	A-BLK	GCP	PLR	M		2			5			9							SALEABLE							
KEY A, BLACK	33482-1762	A-BLK	GCP	PLR	M	1	2			5		7	9	10	11	12	13	14	16	SALEABLE							
KEY A, BLACK	33482-1763	A-BLK	GCP	PLR	M						7								16	SALEABLE							
KEY A, BLACK	33482-1764	A-BLK	GCP	PLR	M					5	6	7	9		11	12	13	14	16	SALEABLE							
KEY A, BLACK	33482-1765	A-BLK	GCP	PLR	M		2			5		7	9			12	13	14	16	SALEABLE							
KEY A, BLACK	33482-1766	A-BLK	GCP	PLR	M					5	6	7	9	10	11	12	13	14	16	SALEABLE							
KEY A, BLACK	33482-1767	A-BLK	GCP	PLR	M					5	6	7	9						16	SALEABLE							
KEY A, BLACK	33482-1768	A-BLK	GCP	PLR	M					5	6	7	9	10					16	SALEABLE							
KEY A, BLACK	33482-1769	A-BLK	GCP	PLR	M	1			4	5	6		8			12	13	14	16	SALEABLE							
KEY A, BLACK	33482-1770	A-BLK	GCP	PLR	M	1	2		4	5	6		8	9	10		12	13	14	15	16	SALEABLE					
KEY A, BLACK	33482-1771	A-BLK	GCP	PLR	M	1			4		6	7	8		10			13	14	15		SALEABLE					
KEY A, BLACK	33482-1772	A-BLK	GCP	PLR	M									10			13	14	15	16	SALEABLE						
KEY A, BLACK	33482-1773	A-BLK	GCP	PLR	M	1	2	3	4	5	6					11	12					SALEABLE					
KEY A, BLACK	33482-1774	A-BLK	GCP	PLR	M									10					15			SALEABLE					
KEY A, BLACK	33482-1775	A-BLK	GCP	PLR	M								9	10					15	16		SALEABLE					
KEY A, BLACK	33482-1776	A-BLK	GCP	PLR	M			3	4				9	10					15	16		SALEABLE					
KEY A, YELLOW	33482-1777	A-YW	GCP	PLR	M																	SALEABLE					
KEY A, BLACK	33482-1778	A-BLK	GCP	PLR	M					5			8									SALEABLE					
KEY A, BLACK	33482-1779	A-BLK	GCP	PLR	M					5	6	7	8	9	10	11	12					SALEABLE					
KEY A, BLACK	33482-1780	A-BLK	GCP	PLR	M			3	4	5	6						13	14				SALEABLE					
KEY A, BLACK	33482-1781	A-BLK	GCP	PLR	M	1			4	5	6	7	8	9	10			13	14	15		SALEABLE					
KEY A, BLACK	33482-1782	A-BLK	GCP	PLR	M	1			4		6	7	8		10		12	13	14	15		SALEABLE					
KEY A, BLACK	33482-1783	A-BLK	GCP	PLR	M											11	12			15		SALEABLE					
KEY A, BLACK	33482-1784	A-BLK	GCP	PLR	M			3														SALEABLE					
KEY A, BLACK	33482-1785	A-BLK	GCP	PLR	M	1				5		7				11	12	13	14	15	16	SALEABLE					
KEY A, BLACK	33482-1786	A-BLK	GCP	PLR	M		2			5		7		9		11	12	13	14	15	16	SALEABLE					
KEY A, BLACK	33482-1787	A-BLK	GCP	PLR	M	1	2			5			9									SALEABLE					
KEY A, BLACK	33482-1788	A-BLK	GCP	PLR	M	1	2					7		9		11	12	13	14	15	16	SALEABLE					
KEY A, BLACK	33482-1789	A-BLK	GCP	PLR	M	1	2			5			9						15			SALEABLE					
KEY A, BLACK	33482-1790	A-BLK	GCP	PLR	M	1	2			5		7		9		11	12	13	14	15	16	SALEABLE					
KEY A, BLACK	33482-1791	A-BLK	GCP	PLR	M	1	2	3														SALEABLE					

MX150 2X10 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET



FOR ADDITIONAL INFORMATION SEE SD-33482-0001

ABBREVIATION	DESCRIPTION	COLOR	MATERIAL
A-BLK	HOUSING, KEYING OPTION A	BLACK	SPS/NYLON GF20
B-LG	HOUSING, KEYING OPTION B	LIGHT GRAY	SPS/NYLON GF20
C-BR	HOUSING, KEYING OPTION C	BROWN	SPS/NYLON GF20
D-GR	HOUSING, KEYING OPTION D	GREEN	SPS/NYLON GF20
A-YL	HOUSING, KEYING OPTION A	YELLOW	SPS/NYLON GF20
C-DG	HOUSING, KEYING OPTION C	DARK GRAY	SPS/NYLON GF20
D-SG	HOUSING, KEYING OPTION D	STONE GRAY	SPS/NYLON GF20
GCP	GROMMET CAP (PLUGGED)	BLACK	SPS/NYLON GF20
GCO	GROMMET CAP (OPEN)	BLACK	SPS/NYLON GF20
PLR	PLR	NATURAL	SPS/NYLON GF20
M-R	MAT SEAL	RUST RED	INHERENTLY LUBRICATED SILICONE
M-B	MAT SEAL	LIGHT BLUE	INHERENTLY LUBRICATED SILICONE

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																				STATUS	COMMENTS	OPTIONAL ATTATCHMENTS SOLD SEPERATELY		
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																						BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20					
KEY A, BLACK	33482-2001	A-BLK	GCO	PLR	M-R																					PLANNED OBSOLESCENCE	SEE 33482-2101			
KEY B, LIGHT GRAY	33482-2002	B-LG	GCO	PLR	M-R																					PLANNED OBSOLESCENCE	SEE 33482-2102			
KEY C, BROWN	33482-2003	C-BR	GCO	PLR	M-R																					PLANNED OBSOLESCENCE	SEE 33482-2103			
KEY D, GREEN	33482-2004	D-GR	GCO	PLR	M-R																					PLANNED OBSOLESCENCE	SEE 33482-2104			
KEY A, BLACK	33482-2006	A-BLK	GCP	PLR	M-R																			20		PLANNED OBSOLESCENCE	SEE 33482-2106			
KEY A, BLACK	33482-2007	A-BLK	GCP	PLR	M-R											11										PLANNED OBSOLESCENCE	SEE 33482-2107			
KEY A, BLACK	33482-2008	A-BLK	GCP	PLR	M-R				4	5	6	7						14	15	16	17					PLANNED OBSOLESCENCE	SEE 33482-2108			
KEY A, BLACK	33482-2009	A-BLK	GCP	PLR	M-R							7									16					PLANNED OBSOLESCENCE	SEE 33482-2109			
KEY A, BLACK	33482-2010	A-BLK	GCP	PLR	M-R										10	11	12								20	PLANNED OBSOLESCENCE	SEE 33482-2110			
KEY A, BLACK	33482-2011	A-BLK	GCP	PLR	M-R	1	2																		20	PLANNED OBSOLESCENCE	SEE 33482-2111			
KEY A, BLACK	33482-2012	A-BLK	GCP	PLR	M-R	1	2									10	11	12							20	PLANNED OBSOLESCENCE	SEE 33482-2112			
KEY A, BLACK	33482-2013	A-BLK	GCP	PLR	M-R	1	2									10	11	12	13	14					20	PLANNED OBSOLESCENCE	SEE 33482-2113			
KEY A, BLACK	33482-2014	A-BLK	GCP	PLR	M-R				3	4	5								14				19			PLANNED OBSOLESCENCE	SEE 33482-2114			
KEY A, BLACK	33482-2015	A-BLK	GCP	PLR	M-R				3	4	5											17				PLANNED OBSOLESCENCE	SEE 33482-2115			
KEY A, BLACK	33482-2016	A-BLK	GCP	PLR	M-R		2																	19	20	PLANNED OBSOLESCENCE	SEE 33482-2116			
KEY A, BLACK	33482-2017	A-BLK	GCP	PLR	M-R																		18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2117			
KEY A, BLACK	33482-2018	A-BLK	GCP	PLR	M-R											10		12	13	14				19		PLANNED OBSOLESCENCE	SEE 33482-2118			
KEY A, BLACK	33482-2019	A-BLK	GCP	PLR	M-R				3	4									14			17		19		PLANNED OBSOLESCENCE	SEE 33482-2119			
KEY A, BLACK	33482-2020	A-BLK	GCP	PLR	M-R				3	4	5								14				17	18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2120		
KEY A, BLACK	33482-2021	A-BLK	GCP	PLR	M-R	1	2		3	4	5					10				14			17	18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2121		
KEY A, BLACK	33482-2022	A-BLK	GCP	PLR	M-R				3	4						10				14			17		19		PLANNED OBSOLESCENCE	SEE 33482-2122		
KEY A, BLACK	33482-2023	A-BLK	GCP	PLR	M-R											10	11	12			15	16	17			20	PLANNED OBSOLESCENCE	SEE 33482-2123		
KEY A, BLACK	33482-2024	A-BLK	GCP	PLR	M-R																15	16	17			20	PLANNED OBSOLESCENCE	SEE 33482-2124		
KEY A, BLACK	33482-2025	A-BLK	GCP	PLR	M-R											10				14			17		19		PLANNED OBSOLESCENCE	SEE 33482-2125		
KEY A, BLACK	33482-2026	A-BLK	GCP	PLR	M-R				4	5						10				14	15		17		19		PLANNED OBSOLESCENCE	SEE 33482-2126		
KEY A, BLACK	33482-2027	A-BLK	GCP	PLR	M-R				4	5						10				14	15		17	18	19		PLANNED OBSOLESCENCE	SEE 33482-2127		
KEY A, BLACK	33482-2028	A-BLK	GCP	PLR	M-R	1		3	4	5	6	7	8	9	10	11		13	14	15	16	17	18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2128			
KEY A, BLACK	33482-2029	A-BLK	GCP	PLR	M-R				4	5	6	7									16	17					PLANNED OBSOLESCENCE	SEE 33482-2129		
KEY A, BLACK	33482-2030	A-BLK	GCP	PLR	M-R				3	4	5								13	14	15			18	19		PLANNED OBSOLESCENCE	SEE 33482-2130		
KEY A, BLACK	33482-2031	A-BLK	GCP	PLR	M-R				4			7										16					PLANNED OBSOLESCENCE	SEE 33482-2131		
KEY A, BLACK	33482-2032	A-BLK	GCP	PLR	M-R				3	4	5								13		15			18	19		PLANNED OBSOLESCENCE	SEE 33482-2132		
KEY A, BLACK	33482-2033	A-BLK	GCP	PLR	M-R											10							17		19		PLANNED OBSOLESCENCE	SEE 33482-2133		
KEY A, BLACK	33482-2034	A-BLK	GCP	PLR	M-R																		17	18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2134		
KEY A, BLACK	33482-2035	A-BLK	GCP	PLR	M-R																16	17	18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2135			
KEY A, BLACK	33482-2036	A-BLK	GCP	PLR	M-R							7		9									17	18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2136		
KEY A, BLACK	33482-2037	A-BLK	GCP	PLR	M-R							7		9													PLANNED OBSOLESCENCE	SEE 33482-2137		
KEY A, BLACK	33482-2038	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10		12					17			19		PLANNED OBSOLESCENCE	SEE 33482-2138		
KEY A, BLACK	33482-2039	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8		10							17			19		PLANNED OBSOLESCENCE	SEE 33482-2139		
KEY A, BLACK	33482-2040	A-BLK	GCP	PLR	M-R							7										17				20	PLANNED OBSOLESCENCE	SEE 33482-2140		
KEY A, YELLOW	33482-2041	A-YL	GCO	PLR	M-R																						PLANNED OBSOLESCENCE	SEE 33482-2141		
KEY A, BLACK	33482-2042	A-BLK	GCP	PLR	M-R											10				14			17	18	19		PLANNED OBSOLESCENCE	SEE 33482-2142		
KEY A, BLACK	33482-2043	A-BLK	GCP	PLR	M-R		2		4								11	12		14							PLANNED OBSOLESCENCE	SEE 33482-2143		
KEY A, BLACK	33482-2044	A-BLK	GCP	PLR	M-R																			18	19		PLANNED OBSOLESCENCE	SEE 33482-2144		
KEY A, BLACK	33482-2045	A-BLK	GCP	PLR	M-R									9	10												PLANNED OBSOLESCENCE	SEE 33482-2145		
KEY A, BLACK	33482-2046	A-BLK	GCP	PLR	M-R	1												12			15	16	17	18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2146		
KEY A, BLACK	33482-2047	A-BLK	GCP	PLR	M-R				3	4	5					10			13	14	15		17	18	19		PLANNED OBSOLESCENCE	SEE 33482-2147		
KEY A, BLACK	33482-2048	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9		11	12	13	14	15	16			18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2148		
KEY A, BLACK	33482-2049	A-BLK	GCP	PLR	M-R				3	4	5	6		8	9									18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2149		
KEY A, BLACK	33482-2050	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6						11	12	13	14	15	16	17	18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2150		
KEY A, BLACK	33482-2051	A-BLK	GCP	PLR	M-R												11	12	13	14	15	16	17	18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2151		
KEY A, BLACK	33482-2052	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	PLANNED OBSOLESCENCE	SEE 33482-2152			
KEY A, BLACK																														

MX150 2X10 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																				STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY		
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																						BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS	
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20					
KEY A, BLACK	33482-2071	A-BLK	GCP	PLR	M-R											11							17		19		PLANNED OBSOLESCENCE	SEE 33482-2171		
KEY A, BLACK	33482-2072	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8			11							17		19		PLANNED OBSOLESCENCE	SEE 33482-2172		
KEY A, BLACK	33482-2073	A-BLK	GCP	PLR	M-R								8							15							PLANNED OBSOLESCENCE	SEE 33482-2173		
KEY A, BLACK	33482-2074	A-BLK	GCP	PLR	M-R	1							8		10					15		17					PLANNED OBSOLESCENCE	SEE 33482-2174		
KEY A, BLACK	33482-2075	A-BLK	GCP	PLR	M-R	1							8	9		11								19	20		PLANNED OBSOLESCENCE	SEE 33482-2175		
KEY A, BLACK	33482-2076	A-BLK	GCP	PLR	M-R										10								19	20			PLANNED OBSOLESCENCE	SEE 33482-2176		
KEY A, BLACK	33482-2077	A-BLK	GCP	PLR	M-R													13			16			19	20		PLANNED OBSOLESCENCE	SEE 33482-2177		
KEY A, BLACK	33482-2078	A-BLK	GCP	PLR	M-R				4										14								PLANNED OBSOLESCENCE	SEE 33482-2178		
KEY A, BLACK	33482-2079	A-BLK	GCP	PLR	M-R				4	5	6	7	8	9	10				14	15	16	17	18	19	20		PLANNED OBSOLESCENCE	SEE 33482-2179		
KEY A, BLACK	33482-2080	A-BLK	GCP	PLR	M-R	1							8		10	11	12	13	14	15		17					PLANNED OBSOLESCENCE	SEE 33482-2180		
KEY A, BLACK	33482-2081	A-BLK	GCP	PLR	M-R	1			3	4			8	9		11		13	14				18	19	20		PLANNED OBSOLESCENCE	SEE 33482-2181		
KEY A, BLACK	33482-2082	A-BLK	GCP	PLR	M-R	1			3	4			8	9	10	11		13	14				18	19	20		PLANNED OBSOLESCENCE	SEE 33482-2182		
KEY A, BLACK	33482-2083	A-BLK	GCP	PLR	M-R	1							8	9	10	11								19	20		PLANNED OBSOLESCENCE	SEE 33482-2183		
KEY A, BLACK	33482-2084	A-BLK	GCP	PLR	M-R	1								9			12										PLANNED OBSOLESCENCE	SEE 33482-2184		
KEY A, BLACK	33482-2085	A-BLK	GCP	PLR	M-R	1																		19			PLANNED OBSOLESCENCE	SEE 33482-2185		
KEY A, BLACK	33482-2086	A-BLK	GCP	PLR	M-R		2	3		5									14					19	20		PLANNED OBSOLESCENCE	SEE 33482-2186		
KEY A, BLACK	33482-2087	A-BLK	GCP	PLR	M-R	1											12	13						19			PLANNED OBSOLESCENCE	SEE 33482-2187		
KEY A, BLACK	33482-2088	A-BLK	GCP	PLR	M-R	1				5	6	7	8				12	13		15				19			PLANNED OBSOLESCENCE	SEE 33482-2188		
KEY A, BLACK	33482-2089	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9			12	13	14	15	16			19			PLANNED OBSOLESCENCE	SEE 33482-2189		
KEY A, BLACK	33482-2090	A-BLK	GCP	PLR	M-R	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16			19	20		PLANNED OBSOLESCENCE	SEE 33482-2190		
KEY A, BLACK	33482-2101	A-BLK	GCO	PLR	M-B																						SALEABLE			
KEY B, LIGHT GRAY	33482-2102	B-LG	GCO	PLR	M-B																						SALEABLE			
KEY C, BROWN	33482-2103	C-BR	GCO	PLR	M-B																						NOT RECOMMENDED	SEE 33482-2154		
KEY D, GREEN	33482-2104	D-GR	GCO	PLR	M-B																						NOT RECOMMENDED	SEE 33482-2155		
KEY A, BLACK	33482-2106	A-BLK	GCP	PLR	M-B																				20		SALEABLE			
KEY A, BLACK	33482-2107	A-BLK	GCP	PLR	M-B											11											SALEABLE			
KEY A, BLACK	33482-2108	A-BLK	GCP	PLR	M-B				4	5	6	7							14	15	16	17					SALEABLE			
KEY A, BLACK	33482-2109	A-BLK	GCP	PLR	M-B							7									16						SALEABLE			
KEY A, BLACK	33482-2110	A-BLK	GCP	PLR	M-B										10	11	12								20		SALEABLE			
KEY A, BLACK	33482-2111	A-BLK	GCP	PLR	M-B	1	2																		20		SALEABLE			
KEY A, BLACK	33482-2112	A-BLK	GCP	PLR	M-B	1	2								10	11	12								20		SALEABLE			
KEY A, BLACK	33482-2113	A-BLK	GCP	PLR	M-B	1	2								10	11	12	13	14						20		SALEABLE			
KEY A, BLACK	33482-2114	A-BLK	GCP	PLR	M-B				3	4	5								14			17		19			SALEABLE			
KEY A, BLACK	33482-2115	A-BLK	GCP	PLR	M-B				3	4	5											17					SALEABLE			
KEY A, BLACK	33482-2116	A-BLK	GCP	PLR	M-B		2																18	19	20		SALEABLE			
KEY A, BLACK	33482-2117	A-BLK	GCP	PLR	M-B																		18	19	20		SALEABLE			
KEY A, BLACK	33482-2118	A-BLK	GCP	PLR	M-B										10		12	13	14					19			SALEABLE			
KEY A, BLACK	33482-2119	A-BLK	GCP	PLR	M-B				3	4									14			17		19			SALEABLE			
KEY A, BLACK	33482-2120	A-BLK	GCP	PLR	M-B				3	4	5								14			17	18	19	20		SALEABLE			
KEY A, BLACK	33482-2121	A-BLK	GCP	PLR	M-B	1	2		3	4	5				10				14			17	18	19	20		SALEABLE			
KEY A, BLACK	33482-2122	A-BLK	GCP	PLR	M-B				3	4					10				14			17		19			SALEABLE			
KEY A, BLACK	33482-2123	A-BLK	GCP	PLR	M-B										10	11	12			15	16	17			20		SALEABLE			
KEY A, BLACK	33482-2124	A-BLK	GCP	PLR	M-B																									



MX150 2X10 BLADE SEALED ASSY MAT SEAL
BOM AND PIN OUT SHEET

ASSEMBLY DESCRIPTION	ASSEMBLY PART NUMBER	COMPONENT				BLOCKED TERMINALS																				STATUS	COMMENTS	OPTIONAL ATTACHMENTS SOLD SEPERATELY	
		THE PRESENCE OF AN ABBREVIATION INDICATES THE PRESENCE OF THAT COMPONENT.				CAVITY WITH A NUMBER INDICATES BLOCKED TERMINAL POSITION CAVITY WITHOUT A NUMBER INDICATES OPEN TERMINAL POSITION																						BACKSHELL WITH RIBS	BACKSHELL WITHOUT RIBS
		HOUSING KEY/COLOR	GROMMET CAP	PLR	MAT SEAL	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20				
KEY A, BLACK	33482-2176	A-BLK	GCP	PLR	M-B									10				13						19	20	SALEABLE			
KEY A, BLACK	33482-2177	A-BLK	GCP	PLR	M-B													13			16			19	20	SALEABLE			
KEY A, BLACK	33482-2178	A-BLK	GCP	PLR	M-B				4										14										
KEY A, BLACK	33482-2179	A-BLK	GCP	PLR	M-B				4	5	6	7	8	9	10				14	15	16	17	18	19	20	SALEABLE			
KEY A, BLACK	33482-2180	A-BLK	GCP	PLR	M-B	1							8		10	11	12	13	14	15		17							
KEY A, BLACK	33482-2181	A-BLK	GCP	PLR	M-B	1			3	4				8	9		11		13	14			18	19	20	SALEABLE			
KEY A, BLACK	33482-2182	A-BLK	GCP	PLR	M-B	1			3	4				8	9	10	11		13	14			18	19	20	SALEABLE			
KEY A, BLACK	33482-2183	A-BLK	GCP	PLR	M-B	1								8	9	10	11							19	20	SALEABLE			
KEY A, BLACK	33482-2184	A-BLK	GCP	PLR	M-B	1									9			12											
KEY A, BLACK	33482-2185	A-BLK	GCP	PLR	M-B	1																		19					
KEY A, BLACK	33482-2186	A-BLK	GCP	PLR	M-B		2	3			5									14				19	20	SALEABLE			
KEY A, BLACK	33482-2187	A-BLK	GCP	PLR	M-B	1												12	13					19					
KEY A, BLACK	33482-2188	A-BLK	GCP	PLR	M-B	1				5	6	7	8					12	13		15			19					
KEY A, BLACK	33482-2189	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9				12	13	14	15	16		19					
KEY A, BLACK	33482-2190	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16		19	20	SALEABLE				
KEY A, BLACK	33482-2191	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6		8		10			13			16			19	20	SALEABLE			
KEY A, BLACK	33482-2192	A-BLK	GCP	PLR	M-B		2						8					13			16			19	20	SALEABLE			
KEY A, BLACK	33482-2193	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6	7	8	9	10			13			16			19	20	SALEABLE			
KEY A, BLACK	33482-2194	A-BLK	GCP	PLR	M-B	1	2	3	4	5	6		8	9	10			13			16			19	20	SALEABLE			
KEY A, BLACK	33482-2195	A-BLK	GCP	PLR	M-B		2											13			16			19	20	SALEABLE			
KEY B, LIGHT GRAY	33482-2196	B-LG	GCP	PLR	M-B	1	2	3	4	5	6	7	8				11					17		19					
KEY B, LIGHT GRAY	33482-2197	B-LG	GCP	PLR	M-B												11					17		19					
KEY A, BLACK	33482-2198	A-BLK	GCP	PLR	M-B	1	2	3				7		9							16			19	20	SALEABLE			
KEY A, BLACK	33482-2199	A-BLK	GCP	PLR	M-B	1	2	3	4	5		7	8	9				13	14	15	16			19	20	SALEABLE			
KEY A, BLACK	33482-2200	A-BLK	GCP	PLR	M-B	1	2	3	4	5						11	12		14			17	18	19	20	SALEABLE			
KEY A, BLACK	33482-2201	A-BLK	GCP	PLR	M-B	1	2							9	10	11				15				19	20	SALEABLE			
KEY A, BLACK	33482-2202	A-BLK	GCP	PLR	M-B		2	3	4	5			8	9							16				20	SALEABLE			
KEY A, BLACK	33482-2203	A-BLK	GCP	PLR	M-B	1	2	3						9										19	20	SALEABLE			
KEY A, BLACK	33482-2204	A-BLK	GCP	PLR	M-B				4	5	6						12			15	16	17	18	19		SALEABLE			