

**SPECIFICATION:**

Contact resistance: 20m ohm max. (initial)

Insulation resistance: 100M ohm min. (at 500V DC)

Dielectric strength: 1,500V AC 50/60 Hz for 1 minute

Service life: Mechanically: 100,000 operations min.

Electrically: 30,000 operations min.

Rating: 12A 125V AC / 250V AC

1/2 HP 125VAC / 1HP 250VAC / 5A 125VAC "L"






Function: (ON) - OFF - (ON) DPDT

KEYWAY  
POSITION

Waterproof rating: IP68

Actuator: Brass / Dull Nickel Plated

( ) = Momentary Function



RoHS Compliant

**CW** INDUSTRIES  
Southampton, Pa. 18966  
Tel 215.355.7080/www.cwind.com

|                      |                 |          |                            |
|----------------------|-----------------|----------|----------------------------|
| Date Drawn: 3-26-12  | Rev. 0          | Unit: mm | Checked By: <i>G. Guld</i> |
| Title: TOGGLE SWITCH | CW P/N: GTB3B17 |          |                            |