

UT302C


[Enlarge](#)
[Download Manual](#)

Infrared Thermometers

SPECIFICATIONS

Basic Functions	Range	Best Accuracy
Temperature Range	-32~650°C	
Display Accuracy	± 1.8°C or ± 1.8%	
Repeatability	± 0.5°C or-0.5%	
Display Resolution	0.1	
Distance to Spot Size	20 : 1	
Response Time		
Spectral Response		
Laser Power	wavelength 630-670 nm	
Display Hold		
°C / °F Selection	✓	
Emissivity		
Temperature Data Hold	✓	
Power	USB (Auto Double Display Backlight) or 9V Battery (6F22)	
Laser Switch	✓	
Search	✓	
Electricity Cut Off Memory	✓	
MAX, MIN temperatures	✓	
DIF, AVG temperatures	✓	
Double Display Backlight	EL	
Sleep Mode	✓	
Tripod mount	✓	
Low Battery Display	✓	

GENERAL CHARACTERISTICS

LCD Size	32 x 29 mm
Product Color	Red and Grey
Product Net Weight	270g
Product Size	169 x 138 x 53 mm
Standard Accessories	Battery, English Manual, USB Cable
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	32 pcs
Standard Carton Measurement	510 x 410 x 330 mm(0.069 CBM Per Standard Carton)
Standard Carton Gross Weight	13kg

*Available at Extra Cost

Specifications and other information are subject to change without further notice.

[Back to main menu](#)