




CATALOG LISTING
19HM4-CB

ISSUE
M
PAGE 1 OF 1
RELEASE NO. PR-23850

REVISIONS
A 0004462
KSR
APR 04

FORMTEK
DRAWN
L J K
19 FEB 99
CHECK
J A F
19 FEB 99
CHECK
AK


WOBBLEFRAM ACTUATOR SEAL



- NOTES**
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF Ø .087 MAX ON .375 ± .002 CENTERS
 - 2 — FOR USE IN TEMPERATURE RANGE -300°F TO +500°F
 - 3 — HERMETICALLY SEALED (METAL-TO-METAL, GLASS-TO-METAL)
 - 4 — ALL EXPOSED PARTS ARE OF CORROSION RESISTANT MATERIALS
 - 5 — TERMINALS ARE TINNED FOR SOLDERING
 - 6 — DO NOT: APPLY MORE THAN 1 1/2 INCH-LBS OF TORQUE WHEN TIGHTENING MOUNTING SCREWS
 - 7 — GOLD ALLOY MOVABLE CONTACT AND GOLD ALLOY STATIONARY CONTACTS
 - 8 — DRY NITROGEN FILL GAS

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



CHARACTERISTICS		ELECTRICAL DATA	SCALE 2 : 1	DO NOT SCALE PRINT
OPERATING FORCE — — — 11.0 OZ MAX		CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ± .030 TWO PLACE (.00) ± .015 THREE PLACE (.000) ± .005 ANGLES ± WEIGHT .014 LB MAX	
RELEASE FORCE — — — 1.5 OZ MIN				
DIFFERENTIAL TRAVEL — — — .004 MAX				
OVERTRAVEL — — — .006 MIN				
		28 VOLTS DC RATING INDUCTIVE — SEA LEVEL — 1/4 AMP 70,000 FT — 1/4 AMP RESISTIVE — SEA LEVEL — 1/2 AMP 70,000 FT — 1/2 AMP		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[19HM4-CB](#)