



Shape

KPEG620AN




Rated Frequency (Hz)	2,800±500
Operating Voltage Range (V.D.C.)	60~250 AC/DC
Current Consumption (mA)	Max.18@220VDC/AC
Sound Pressure Level (dB)	Min.85dB@30cm / 220VDC/AC
Rated Voltage	220VDC/AC
Tone	Continuous
Operating Temperature (°C)	-30 ~ +85
Storage Temperature (°C)	-40 ~ +95
Weight (Gram)	51.0
Material	奇美PA-777D環保(Black)

Dimension



Top View



Characteristic / Schematic Diagram