

.100" c.l. Shunts

SH-1

Mates with: TSHS, TSHR, TSHC, BSTS, BSTC, TSHCRE, LTSRH, LTSHRE, BSTCM, LTSHCRE, TSHRE, TSHSM, TSHCR

Plating Options

T = 200 μ in tin/lead over entire pinG = 10 μ in gold contact area, gold flash on tail

Other plating options available upon request

Shunt Style

Contact Withdrawal Force Contact Insertion Force

4 ounce (NOM)

4 ounce (NOM)

01

4 ounce (NOM)

4 ounce (NOM)

02


5 ounce (NOM)

7 ounce (NOM)


03

Handle Option


H




Product cut to specific sizes is noncancelable/nonreturnable.
Parts are subject to change without notice.




Style -01



Style -02



Style -03



Style -02 - H

Materials & Performance Specifications



	HIGH TEMPERATURE		HIGH TEMPERATURE
Insulator	PBT Thermo Plastic	Temperature Range	-55°C to +125°C
Terminal	Phosphor Bronze	Current Rating	2 amperes
Insulation Resistance	5,000M Ω minimum	Plating	All Plating Options over 50 μ in Ni
Flammability	UL 94V-O		

