

LFM LED 18353LG



LFM LED T70 LG 107 840 5DBA NA

LFM LED is Luxo's most cost-effective LED Magnifier. A die-cast aluminum housing and flexible, 30" spring-balanced L-arm ensure the magnifier can be placed in any position. Auto shut-off and dimming features ensure energy savings. LFM LED is suitable for a variety of applications. Old item no. 18353LG. 2.25X lens. Weighted base. Color: light grey.



Lightsource

Number of lamps	1
Lamp power (W)	10
Lightsource	LED
CRI and/or Color Temperature	80 CRI, 4000K
Lumen/Watt	51
Lumen Out	505

Optic

Primary Lens (D)	5
Working distance (mm)	200
Magnification (X)	2.25

Technical data

Maximum ambient temperature (°C)	25
IP classification	20

Electrical data

Maximum frequency (Hz)	60
Minimum frequency (Hz)	50
Maximum voltage (V)	120
Voltage from (V)	100
Total consumption (W)	10

Dimensions

Net weight (kg)	0
Arm length (in.)	30

Body

Body color	Grey
------------	------

Termination

Mounting	Table/desk base
----------	-----------------

LFM LED
18353LG



LFM LED T70 LG 107 840 5DBA NA

LFM LED is Luxo's most cost-effective LED Magnifier. A die-cast aluminum housing and flexible, 30" spring-balanced L-arm ensure the magnifier can be placed in any position. Auto shut-off and dimming



Photos

