

Smart USB 550VA Tower Line-Interactive 120V UPS with USB port and Watchdog service monitoring software

MODEL NUMBER: **SMART550USBWD**



Highlights

- 550VA tower 120V line interactive UPS with WatchDog software
- Corrects brownouts as low as 89V without using battery power
- 3 UPS battery supported outlets, 3 surge-only outlets
- USB port, TEL/DSL/ethernet protection
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

Package Includes

- SMART550USBWD UPS System
- USB and telephone interconnection cables
- Tripp Lite WatchDog and PowerAlert Software on CD-ROM
- Instruction manual with warranty information

Description

Tripp Lite's SMART550USBWD provides unattended systems (including kiosks, web/email servers, security system computers and more) with a single-purchase solution for 100% availability, including a UPS System and WatchDog Service Monitoring/Reboot Software. In addition to completely bulletproofing equipment against two common causes of downtime (blackouts and computer service lockup)

SMART550USBWD models save money by providing two availability products for less than the price of a single solution.

The line-interactive UPS System offers voltage regulation, surge suppression and long lasting battery support. Internal UPS circuits support systems for up to 30 minutes during power failures. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 89 volts back to normal 120V levels without using battery power. Offers complete power protection in an attractive black tower configuration. Includes 3 battery supported outlets for computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support. USB port works with PowerAlert Software (included) to enable optional unattended system shutdown without data loss in the case of an extended power failure, USB cable included. Built-in single line RJ11 phone suppression jacks protect modem or other peripheral with a standard dialup/DSL phone connection. Built-in audible alarm and 4 front panel LEDs indicate line power status, battery power status, battery low/replace status and voltage boost operation. 550VA/300 watt power handling ability. Offers 4.6 minutes battery runtime with a full load of 550VA/300 watts and 14.8 minutes with a half load of 275VA/150 watts. Supports battery replacement via built-in access panel. \$200,000 [connected equipment insurance](#) (USA and Canada Only).

WatchDog Software (included) automatically reboots locked-up or poorly performing system service applications. Set CPU- and memory-usage thresholds and monitor service performance in one application. Together with the UPS System, WatchDog Software eliminates the #1 reason for costly service calls—the need to reboot locked systems.* WatchDog Software runs directly on your computer, eliminating the need for a separate hardware device. If the system fails to reboot, WatchDog Software automatically directs PowerAlert Software to reboot the computer and connected equipment by powering down and restarting the UPS System. WatchDog Software supports Windows® NT, 2000 and XP systems. *Server Technology study*

Features

- SMART550USBWD line interactive UPS system offers voltage regulation and battery support in addition to complete AC and dialup/DSL modem line surge suppression
- Includes Tripp Lite's WatchDog Service Monitoring/Reboot Software as well as PowerAlert, Tripp Lite's Network Power Management Software
- WatchDog Software automatically reboots locked-up or poorly performing system service applications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Supports CPUs for up to 30 minutes during power failures
- Supports a max load of 550VA/300 watts for 4 minutes and a half load of 275VA/150 watts for 15 minutes
- Automatic Voltage Regulation (AVR) circuits correct brownouts as low as 89 volts without using battery power
- 550VA/300 watt power handling ability
- Includes 3 battery supported outlets, plus 3 additional surge suppression-only outlets, 6 foot AC line cord (all NEMA 5-15)
- USB port enables unattended shutdown without data loss during extended power failures. Includes USB cable
- Attractive black tower configuration
- Built-in RJ-style phone suppression jacks protect modem or other peripheral with a dialup or DSL line phone connection
- Built-in audible alarm and 4 front panel LEDs indicate UPS system and line power status
- Supports battery replacement via built-in access panel
- Compatible with 120V/60Hz applications for USA, Canada, Mexico and more
- \$200,000 [connected equipment insurance](#) (USA and Canada Only)

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	550
Output Watt Capacity (watts)	300
Nominal Output Voltage(s) Supported	115V; 120V
Frequency compatibility	60 Hz
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	6 5-15R outlet(s)
Surge suppression only outlets	3 UPS outlets, 3 surge-only outlets
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
Phase	Single-Phase
BATTERY	
Full load runtime (minutes)	4 min. (300w)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Half load runtime (minutes)	15 min. (150w)
DC system voltage (VDC)	12
Battery recharge rate (included batteries)	Less than 3.6 hours from 10% to 90%
Replacement battery cartridge (internal UPS battery replacement)	RBC51
Battery Access	Battery access door
Battery replacement description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage regulation description	Automatic voltage regulation (AVR) maintains line power operation with input voltage as low as 89
Undervoltage correction	Input voltages between 89 and 104V are boosted by 14%
LEDS ALARMS & SWITCHES	
LED Indicators	4 LEDs indicate line power, battery power, overload and battery low/replace status
Alarms	Audible alarm indicates power-failure and low-battery conditions
Alarm cancel operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	480
UPS AC suppression response time	Instantaneous
UPS Dataline suppression	1 line TEL/DSL (1 in / 1 out)
EMI / RFI AC noise suppression	Yes
PHYSICAL	
Installation form factors supported with included accessories	Tower
Installation form factors supported with optional accessories	Wallmount (UPSWM - tower mounting kit)
Primary form factor	Tower
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	8.5 x 5 x 6.5
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	21.6 x 12.7 x 16.5
UPS / Power Module weight (lbs)	14.4
UPS / Power Module weight (kg)	6.5



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

UPS Shipping dimensions (height x width x depth / inches)	12 x 8.2 x 9.2
UPS Shipping dimensions (height x width x depth / cm)	30.5 x 21 x 23.5
Shipping weight (lbs)	16
Shipping weight (kg)	7.3
UPS housing material	PVC
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	65.1
Battery mode BTU / hr. (full load)	358.4
AC mode efficiency rating (100% load)	94%
COMMUNICATIONS	
Communications interface	USB (HID enabled)
PowerAlert software	PowerAlert and Watchdog software included
Communications cable	USB interface cable included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer time	2-4 milliseconds
Low voltage transfer to battery power (setpoint)	89
High voltage transfer to battery power (setpoint)	139
SPECIAL FEATURES	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Hot swappable batteries
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 Ultimate Lifetime Insurance

Related Items

Optional Products

Model Number	Description	Qty.
DCATV	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	1
DNET1	Network Surge Suppressor - Essential protection for data and communication lines	1
DTEL2	Network Surge Suppressor - Essential protection for data and communication lines	1
UPSWM	Wallmount Bracket and installation accessories (4 washers, 4 screws, 1 Velcro safety strap)	1
U022-010	10-ft. USB2.0 A/B Gold Device Cable (A Male to B Male)	1
WEXT5-500-1500	5-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 1500VA or less	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at:

<http://www.tripplite.com/sku/SMART550USBWD>.

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SMART550USBWD](#)