

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0436451000

Status:

Active

Overview:

Micro-Fit, 3.0™

Description:

3.00mm (.118") Pitch Micro-Fit 3.0™ Receptacle Housing, Single Row, 10 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-43650 (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Overview

Product Literature Order No

Product Name

Crimp Housings

43645

Micro-Fit, 3.0™

USA-106

Micro-Fit 3.0™

Physical

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Compliant

Keying to Mating Part

Lock to Mating Part

Material - Resin

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface (in)

Pitch - Mating Interface (mm)

Stackable

Temperature Range - Operating

10

Black

94V-0

Female

No

None

Yes

Polyester

1

Bag

No

0.118 In

3.00 mm

No

-40°C to +105°C

Electrical

CSA

Current - Maximum

TUV

UL

LR19980

5A

R72081037

E29179

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-43650

SDA-43645-****




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Not Halogen-Free

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

43645Series

Mates With

43640 Micro-Fit 3.0™ Plug Housing, 43650 Micro-Fit 3.0™ Header

Use With

43030 Micro-Fit 3.0™ Crimp Terminal