


SPECIFICATIONS

STEP ANGLE	1.8°±5%	VOLTAGE	12V
NO. of PHASE	4	CURRENT/PHASE	0.4A
Inultion Resistant	100Mohm(500VDC)	INDUCTANCE/PHASE	28±20% μ H
Ambient Temperature	-20~40℃	RESISTANCE/PHASE	30±10% Ω
Operate_Temperature	110℃ Max	HOLDING_TORQUE	3.4kg.cm
WEIGHT	0.34kg Max		

WIRING DIAGRAM



FIGURE

UNIT:mm

