


IEC 60320 Inlet / Outlet With Fuseholder

161-R3014G21-E


KOBICONN

IEC 60320 Inlet / Outlet With Fuseholder



PANEL CUT-OUT

A	
Add to PN	Dimension
10	1.0
12	1.2
15	1.5
17	1.7
20	2.0
25	2.5



Dimensions: mm

SPECIFICATIONS

Rating:	10A, 250VAC
Insulation Resistance:	Over 100MΩ at 500VDC
Dielectric Strength:	2000VAC for 1 Minute

MATERIALS

Body:	Black Glass-Fiber Thermoplastic
RoHS Compliant	

Tolerance

X.XX±0.1
XX.XX±0.2
XXX.XX±0.3

Date Last Revised: 3-5-2010

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC- 301378

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

161-R3014G21-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[161-R3014G21-E](#)