






- ① MATERIAL: TELLURIUM COPPER.
- ② MATERIAL: BERYLLIUM COPPER.
- ③ FINISH: SILVER PLATE 5 μ M [200 μ IN] THICK MIN.
OVER 1.2 μ M [50 μ IN] THICK MIN. NICKEL
OVER 0.1 μ M [5 μ IN] THICK COPPER FLASH.
- ④ FINISH: SILVER PLATE 5 μ M [200 μ IN] THICK MIN.
OVER 1 μ M [40 μ IN] THICK MIN. NICKEL.
- ⑤ MATERIAL: ACETYL (DELTRIN).

2.55[.100]	6.35[.250]	1	SOCKET, 3MM, #12-14	194032-7
3.68[.145]	7.24[.285]	3	SOCKET, 3MM, #10	194032-6
4.60[.181]	8.42[.331]	2	SOCKET, 3MM, #8	194032-5
ØB	A DIM	FIGURE #	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		OWN RNP CHK - 28/SEP/95		AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm [in]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		SOCKET ASSEMBLY	
MATERIAL -		FINISH -		SIZE CAGE CODE DRAWING NO A2 00779 C=194032	
		WEIGHT -			
CUSTOMER DRAWING				SCALE SHEET OF REV 1 1 B	