





T&B Rigid Fittings




NOTES:

CONDUIT BODY IS SHOWN

- MATERIAL:
BODY AND COVER: 316 STAINLESS STEEL
SCREWS AND WASHER RETAINERS: 18-8 STAINLESS STEEL
GASKET AND WASHER SEALS: SOLID NEOPRENE (-20°F TO 170°F)
- FINISH:
COVER: MIRROR POLISHED
BODY: POLISHED
GASKET AND WASHER SEALS: BLACK IN COLOR
- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- ALL HUBS: NPT THREADS
- SS CONDUIT BODIES AND COVERS ARE ASSEMBLED.
- TWO SCREW COVER STYLE SHOWN. TRADE SIZES 1-1/2" & 2" SHALL HAVE (4) SCREW STYLE.
- UL LISTED AND CSA CERTIFIED.

ASSEMBLED CONDUIT BODY IS SHOWN



LB68SST	2" LB STYLE CONDUIT BODY 88.0 CU IN; MAX. 3 WIRE 1/0	11.000"	3.820"	4.810"	2.900"	9.797"	9.125"
LB58SST	1-1/2" LB STYLE CONDUIT BODY 44.0 CU IN; MAX. 3 WIRE #1	8.992"	2.813"	3.800"	2.450"	7.938"	7.125"
LB48SST	1-1/4" LB STYLE CONDUIT BODY 23. CU IN; MAX. 3 WIRE #2	7.734"	2.200"	3.315"	2.200"	6.730"	5.810"
LB38SST	1" LB STYLE CONDUIT BODY 13.0 CU IN; MAX. 3 WIRE #4	6.563"	1.850"	2.913"	1.750"	5.625"	5.000"
LB28SST	3/4" LB STYLE CONDUIT BODY 8.0 CU IN; MAX. 3 WIRE #6	5.671"	1.645"	2.530"	1.400"	4.921"	4.300"
LB18SST	1/2" LB STYLE CONDUIT BODY 5.8 CU IN	5.070"	1.450"	2.250"	1.150"	4.320"	3.700"
CAT.NO.	TRADE SIZE ; VOLUME CONTENT; MAX. NUMBER & SIZE OF WIRES	DIM. "A"	DIM. "B"	DIM. "C"	DIM. "D"	DIM. "E"	DIM. "F"

GENERAL NOTES

- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.

REVISIONS

** SEE ERN (****)
FOR APPROVAL SIGNATURES
& RELEASE DATE.
PROJECT NO: ****

Thomas & Betts
www.tnb.com

DESCRIPTION:

LB STYLE ASSEMBLED SS CONDUIT BODIES

ORIGINAL PROJECT NO / (ERN NO)

RD55769 / (2012664)

SHEET NO:

1 OF 1

REV. NO:

1

DRAWING NO:

WSD-000530

THIS DRAWING IS INTENDED FOR DESCRIPTIVE PURPOSES ONLY. AND THE RIGHT IS RESERVED TO DEViate FROM ANY OF THE DETAILS SHOWN HEREON.

© Thomas & Betts - Proprietary. All Rights Reserved