

Part Number: 5530221200F

General Description	
Series	553
Configuration	3 mm Lens
Description	3 mm Bi -Level CBI
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Left
Lens Style	Tinted, Diffused
Viewing Angle	60
LED Centerline	2.54mm

Absolute Maximum Ratings (Ta = 25Â°)	
Solder Temperature	260 for 5 secs
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics		
	LED Position: 1	LED Position: 2
Color	Red	Green
LED Type	Low Current	Low Current
Peak Wave Length	635	565
Luminous Intensity Min	1	1
Luminous Intensity Typical	1.6	1.6
Forward Voltage Typical	1.7	1.9
Forward Voltage Max	2.2	2.2
Power Dissipation Max	20mW	20mW



5530221200F

check stock



This is a
RoHS Compliant Product
To learn more click here