




REV.	DESCRIPTION	DATE
A	RELEASE	2012.11.12

NOTES:
Insulator Material: PBT, UL 94V-0
Contact Plating: flash gold
Contact Material: Phosphor Bronze

Current Rating : 1A AC,DC
Contact Resistance: 20M Ω Max.
Dielectric Withstanding: AC 500V
Insulator Resistance: 1000M Ω Min.
Operating Temp.: -40°C~+105°C

NUMBER OF POSITIONS	DIMENSION		
	A	B	C
06	2.54	8.00	11.80
08	3.81	9.27	13.07
10	5.08	10.54	14.34
12	6.35	11.81	15.61
14	7.62	13.08	16.88
16	8.89	14.35	18.15
20	11.43	16.89	20.69
24	13.97	19.43	23.23
26	15.24	20.70	24.50
30	17.78	23.24	27.04
34	20.32	25.78	29.58
40	24.13	29.59	33.39
44	26.67	32.13	35.93
50	30.48	35.94	39.74
60	36.83	42.29	46.09
64	39.37	44.83	48.63
66	40.64	46.10	49.90
68	41.91	47.37	51.17
70	43.18	48.64	52.44
74	45.72	51.18	54.98
76	46.99	52.45	56.25
80	49.53	54.99	58.79

Mating Part Number		
3221-ALL		

UNLESS TOLERANCE		DRAW BY		CnC Tech,LLC Part NO. 3230-XX-0103-00		
GENERAL	ANGLE	DESIGN BY				
X. ± 0.30	X.* ± 3.0°	CHECK BY				
.X ± 0.20	.X* ± 2.0°	APPROVE BY				
.XX ± 0.15	.XX* ± 1.0°					
.XXX ± 0.10	.XXX* ± 0.5°					
		SCALE	SHEET	UNIT	DRW NO:	REV: A
		1:1	1/1	MM		