








LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J			D2	REVISED(ECR-14-018055)	17MAR15	W.C	V.P



- 注記
- 材料：ハウジング - 66 ナイロン (UL94V-0)
ポスト - 錫めっき済黄銅
 - 適用製品規格：108-5385
 - 嵌合相手製品型番：P/N 177534, 179872



- NOTES;
- MATERIAL : HOUSING - 66NYLON (UL94V-0)
POST - PRE-TIN BRASS
 - PRODUCT SPEC : 108-5385
 - MATING COUNTER PART NUMBER : P/N 177534 ,179872

全箇所
ALL PLACES

4~8極
4~13 Pos.

3ヶ所
3 PLACES

3 極品
3 Pos.


1ヶ所
1 PLACES

2 極品
2 Pos.

1ヶ所
1 PLACES

OBSOLETE:
1-177537-2
177537-9

30.0	34.2	35.0	13	9-	↑ -3	7-	↑ -3	5-	↑ -3	3-	↑ -3	1-	↑ -3
27.5	31.7	32.5	12	9-	-2	7-	-2	5-	-2	3-	-2	1-	-2
25.0	29.2	30.0	11	9-	-1	7-	-1	5-	-1	3-	-1	1-	-1
22.5	26.7	27.5	10	9-	-0	7-	-0	5-	-0	3-	-0	1-	-0
20.0	24.2	25.0	9	8-	-9	6-	-9	4-	-9	2-	-9	1-	-9
17.5	21.7	22.5	8	8-	-8	6-	-8	4-	-8	2-	-8		-8
15.0	19.2	20.0	7	8-	-7	6-	-7	4-	-7	2-	-7		-7
12.5	16.7	17.5	6	8-	-6	6-	-6	4-	-6	2-	-6		-6
10.0	14.2	15.0	5	8-	-5	6-	-5	4-	-5	2-	-5		-5
7.5	11.7	12.5	4	8-	-4	6-	-4	4-	-4	2-	-4		-4
5.0	9.2	10.0	3	8-	-3	6-	-3	4-	-3	2-	-3		-3
2.5	6.7	7.5	2	8-177537-2		6-177537-2		4-177537-2		2-177537-2		177537-2	
C	B	A	極数 Pos.	青 BLUE	黒 BLACK			赤 RED		黄 YELLOW		自然色 NATURAL	
				製品型番 PART No.									



RECOMMENDABLE P.C.BOARD LAYOUT
推奨基板寸法
(板厚 1.0~1.6)
(B.C.B THK:1.0~1.6)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位： 耗
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0-PLC ±

1-PLC ±

2-PLC ±

3-PLC ±

4-PLC ±

ANGLES ±

FINISH
仕上

10以下：±0.2

10を超え 30以下：±0.25

30を超え 100以下：±0.3

角座：±0.3

MATERIAL
材料
SEE NOTE 1

DWN
S.KANEKI
140CT92

CHK
A.ONO
140CT92

APVD
S.KUBOUCHI
250CT95

PRODUCT SPEC
製品規格
SEE NOTE 2

APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

TE Connectivity

POST HDR ASSEMBLY
2.5mm PITCH METRIC INTERCONNECT SYSTEM

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-177537

RESTRICTED TO
—

SCALE
尺度 10:1

SHEET
1 OF 1

REV
D2

1470-19 (3/11)