




REV.	DATE	DESCRIPTION
NC	06/11/00	INITIAL RELEASE



CRIMP NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .255"



RECOMMENDED
CABLE STRIPPING DIM'S

DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS	APPROVALS	DATE	 Connex Connector Corporation			
1 BODY	BRASS	NICKEL	DIMENSIONS IN [] ARE IN INCHES FOR CUSTOMER REFERENCE ONLY UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-315 = ± 1 315-1000 = ± 1.6 1000-2000 = ± 2.4	DRAWN G.R.S.	06/11/00				
2 INSULATOR	TEFLON	NATURAL		CHECKED		TITLE BNC R/A CRIMP PLUG (RG-59/U CABLE)			
3 CONTACT PIN	BRASS	GOLD		ISSUED		SIZE	FSCM NO.	DWG. NO.	REV.
4 FERRULE	COPPER	NICKEL				A	99001	112960.DWG	NC
5						SCALE	NA	PART NO.	112960
6						SHEET			1 OF 1
7									
8			DO NOT SCALE DRAWING						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112960](#)