



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS		VALUE
D.C. RESISTANCE	2-4	@20°C	0.075 ohms max.
D.C. RESISTANCE	9-8	@20°C	0.075 ohms max.
D.C. RESISTANCE	8-7	@20°C	0.075 ohms max.
INDUCTANCE	2-4	10kHz, 100mVAC, Ls	17uH ±10%
CAPACITANCE	2-9	100kHz, 100mVAC, Ls	20pF max.
DIELECTRIC	1-9	tie(4+5), 6000VAC, 3 second	5000VAC, 1 minute
URNS RATIO	(2-4):(9-8)		1.25:1, ±2%
URNS RATIO	(2-4):(8-7)		1.25:1, ±2%

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0222 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750341278
00	11/11	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750341278	SPECIFICATION SHEET 1 OF 1