




REVISIONS									
REV	DATE	DESCRIPTION	BY	CHK	APPD	DATE	DESCRIPTION	BY	CHK
0	RLSE APR 2275	MAS 88-4837-21							
A		REVISED ECN-802959							
B		REVISED ECN 803043							
C		REV PER ECN 805426							

- 1. DIMENSIONS IN BRACKETS ARE IN INCHES.
- △ MATERIAL:
RECEPTACLE CONTACTS - PHOSPHOR BRONZE.
RECEPTACLE SHIELD - COPPER ALLOY.
HOUSING - UL RECOGNIZED 94V-0 RATED THERMOPLASTIC, COLOR: BLACK.
- △ PLATING:
RECEPTACLE CONTACTS - GOLD FLASH PLATED ON MATING END, TIN-LEAD PLATED .0030 MIN [.000120 MIN] THICK ON SOLDER TAIL ALL OVER .0013 MIN [.000050 MIN] THICK NICKEL.
- △ PLATING:
RECEPTACLE SHIELD - .0025 MIN [.000100 MIN] THICK BRIGHT TIN-LEAD OVER .00076 MIN [.000030 MIN] THICK NICKEL.
- 5. RECEPTACLE ASSEMBLY MATES WITH 8 PIN 9.00±.10 [.354±.004] DIAMETER PLUG.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± .005 3 PLC DEC ± 0.001 [.013] ANGLES ± 0°30'		DR 1-24-89 P.COSMOS CHK 1-24-89 C.OHL APPO 1-24-89 B.H.ROSSER APPO 1-24-89 E.C.RYERS PRODUCT SPEC 108-1225	AMP INCORPORATED Murrysville, Pa. 17068	
FINISH -△△	APPLICATION SPEC	SIZE D	FSCH NO 00779	DRAWING NO 749232
WEIGHT		SCALE 5:1	SHEET 1 OF 1	

CUSTOMER DRAWING