



WCB44

WEJTAP CONN BLU

ACTIVE



Electrical division

☒ [Email Datasheet](#) [Print Datasheet](#)

FCI Brings You More

☒ [Contact our sales/technical support](#)

☒ [Sample request](#)

€ [Price request](#)

Download document

Literature

- [> Wejtap Material Safety Data Sheet - Power Cell](#)
- [> Wejtap Material Safety Data Sheet - Black Powder Solvent](#)
- [> Wejtap Product Focus](#)
- [> Wejtap Brochures](#)
- [> Connector Theory and Application Brochure](#)

Application Tooling

- [> Electrical Tooling](#)

Specifications

Dimensional	Physical	Approvals / Certifications	Other Features
Dimensional			
Conductor Size (Run - Diameter)			0.6 to 0.684
Conductor size (Run - Max)			336.4-18/1
Conductor size (Run - Min)			3364
Conductor Size (Run - mm)			15 mm² to 17 mm²
Conductor Size (Run)			336.4 336.4-18/1
Conductor size (Tap - Max)			2/0-6/1
Conductor size (Tap - Min)			2/0
Conductor Size (Tap)			2/0-6/1 2/0
Conductor Type (Run)			AAC ACSR
Wire Size			AWG
Wire Size (Tap - Diameter - in)			0.364 to 0.562
Wire Size (Tap - mm)			9 mm² to 14 mm²
Wire Type (Tap)			ACSR AAC Copper
Physical			
Color Code			Blue
Approvals / Certifications			
UL Listed			No
CSA Certified			No
Other Features			
Installation Tool			WTRB
Booster			WPBB Box 25
UPC			78181087360
Keyw ord			w ejtap