

1

2

3

4

"A" EQUAL SPACES

.100 = "B"

TOL NON-ACCUM

STYLE "B"

A

B

C




D

A


B

C

D



998ZLF CONTACT

THIS HOLE PATTERN APPLIES TO BOTH
STYLE A AND STYLE B CONTACTS.

NOTE ROHS INFORMATION

- The "LF" products meet European Union Directives and other country regulations as described in 65-22-008.
- Packaging spec: see 65-14-920

NOTES:

- INSULATOR MATERIAL:
GLASS FILLED POLYESTER (PCT),
RATED UL 94V-0, COLOR BLACK.
- CONTACT MATERIAL:
OUTER SHELL: PHOSPHOR BRONZE.
INNER CONTACT: BERYLLIUM COPPER.
- CONTACT PLATING:
OUTER SHELL: 200u" TIN/LEAD PER SAE AMS-P-81728
OUTER SHELL: 200u" TIN FOR LEAD FREE VERSION
OVER 100u" NICKEL PER QQ-N-290.
INNER CONTACT: #4(30), 200u" TIN/LEAD PER SAE-AMS-P-81728
INNER CONTACT: #4(30), 200u" TIN FOR LEADFREE VERSION
OVER 100u" NICKEL PER QQ-N-290.
- COMPLIANT PRESS FIT IN $\phi .040 \pm .003$ PLATED
HOLE, RECOMMENDED DRILL SIZE 1.15 MM
FOR .090 TO .130 THICK BOARD.

REV F - 2006-04-17

1

2

3

4

www.fciconnect.com

surface
ISO 1302tolerance std
ISO 406 ISO 1101projection
A3inch
Scale
1:1

TOLERANCES UNLESS OTHERWISE SPECIFIED

ANGULAR

LINEAR

0.X ±0.1

0.XX ±0.1

0.XXX ±0.1

Product family

SOCKET

Spec ref RELEASED

Dr D-WOLFORD 2000/02/14

Eng A-VASBINDER 2000/02/14

Chr A-VASBINDER 2000/02/14

Appr A-VASBINDER 2000/02/14

rev

ecn no

dr

date

H LS07-0271 HLE 2007/10/29

J LS07-0299 HLE 2007/11/20

K LS08-0038 STG 2008/02/01

L LS08-0051 HLE 2008/02/11

- - - -

G LS07-0141 HLE 2007/05/21



PRESS FIT DIP SOCKET

DPF

catalog no

SEE TABLE

dwg no

58707

CUSTOMER

sheet 2 of 2

Rev.

L