

☐ Cable Ties

☐ Cable Ties with Fasteners

☐ Cable Tie Tools

☐ Clamps and Clips

☐ Mounts

☐ Heavy Duty Mounts

☐ Wiring Duct

☐ Solid Wall

☒ Slotted Wall

☐ High Density Slotted Wall

☐ Covers

☐ Accessories

☐ Wiring Protection

☐ Labels, Printers and Software

☐ Pre - Terminated Networking

☐ Copper Network Solutions

☐ Fiber Network Solutions

☐ Jacks and Wall Plates

☐ Residential Solutions

☐ Racks - Cable Management

☐ Surface Raceway Systems

SL1X1G4

Slotted Wall Duet1" X 1" NonAdhesive, PVC, Gray, 120' / carton


Article Number: 181 - 11013
Part Number: SL1X1G4
Type: SL1x1
Material: PVC extrusion



1. Base Data

Part No.	SL1X1G4
Type	SL1x1
Color	Gray
Features	Slotted wall duct features break -away fingers which proved additional access for wire leads. Slotted wall duct is manufactured with two score lines. The first score line is at the base of the finger, allowing the finger to be bent and broken away when a greater opening is required. The second score line is lower, allowing a section of the sidewall to be easily removed by cutting the sidewall down to the lower score line. Use HellermannTyton TDNT notching tool and snap out the desired section. Both score lines proved smooth edges to ensure worker safety. Strong fingers prevent unwanted breaking. The individual finger is easily deflected outward, allowing ready positioning of the wires within the slotted wall duct. Restricted opening design in the finger of the duct helps keep wires in place. Restriction also prevents unintended removal of wires and permits any individual wireto be traced without disconnection. PVC Material Smooth Edges Cover is Flush with Side of Duct Non Slip Cover Professional Appearance

2. Product Dimensions



Length (L)	6 ft / 1.83 m
Width (W)	1.00 " / 25.40 mm
Width (W2)	1.00 " / 25.40 mm
Width (W3)	10.2 mm
Width (W4)	1.00 " / 25.40 mm
Width (W5)	.75 " / 19.05 mm
Height (H)	1.05 " / 26.7 mm
Height (H2)	.75 " / 19.1 mm
Mounting Hole Centers	4.00 " / 101.60 mm

4. Material and Specifications

Material	Polyvinylchloride (PVC)
Material Shortcut	PVC extrusion
Certification	CSA / UL
CSA Certified	Yes
Flammability	self -extinguishing
Material Specification	RoHS
Operating Temperature	+122 Â°F (+50 Â°C)

Logistic and Packaging

Packaging Type	carton
Pkg. Qty.	120 ft / 36.6 m
Carton Qty.	120
UPC	08930604832

Miscellaneous

UL Recognized (US and Canada)	Yes
Width (W3)	.40 "

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)

Customers Who Bought This Item Also Bought

	Wiring Duct Cover Width 1.00" PVC, Gray, 120' / Pkg. Qty. Part No: TC1G4 Article No: 181 - 91004
	Wiring Duct Cover Width 2.00" PVC, Gray, 120' / Pkg. Qty. Part No: TC2G4 Article No: 181 - 92005
	Slotted Wall Duct - 2" X 2" Non -Adhesive, PVC, Gray, 120' / carton Part No: SL2X2G4 Article No: 181 - 22024
	Wiring Duct Cover Width 1.50" PVC, Gray, 120' / Pkg. Qty. Part No: TC1.5G4 Article No: 181 - 91507
	Cable Tie, 50 lb. 15.35" Max. Bun. Dia. 4.33" PA66, Black, 100/pk Part No: T50L0C2 Article No: 111 - 00445

This product was found in [Wiring Duct](#) > [Slotted Wall](#)