

NOTES: UNLESS OTHERWISE SPECIFIED

REVISIONS		DATE	APPROVED
LTR	DESCRIPTION		

1. P/N: 9260BLK
HOUSING: MOLDED NYLON.
FRAME: BRASS. NICKEL PLATED.
CONTACT: BeCu OR PHOSPHOR BRONZE. NICKEL PLATED.

2. P/N: 9260RED
HOUSING: MOLDED NYLON.
FRAME: BRASS. NICKEL PLATED.
CONTACT: BeCu OR PHOSPHOR BRONZE. NICKEL PLATED.


3. P/N: 9230
BODY & FITTINGS: BRASS. NICKEL PLATED.
PIN: BRASS. GOLD PLATED.
DIELECTRIC: PTFE.

4. P/N: 0482
HOUSING: MOLDED DELRIN. BLACK.

5. P/N: W-600/0
18AWG 65X36 TINNED COPPER
0.144 [3.66] O.D. PVC INSULATION

6. P/N: W-600/2
18AWG 65X36 TINNED COPPER
0.144 [3.66] O.D. PVC INSULATION

7. PERFORMANCE:
MAXIMUM CURRENT: 4.0 AMPS
MAXIMUM VOLTAGE: 5000 W.V.D.C.
MAXIMUM TEMPERATURE: 221°F [105°C]



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ±
--	--	---