

D-SUB cable - VS-09-DSUB-20-LI-5,0 - 1656259

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Assembled D-SUB cable, shielded, 9-pos., stranded (7-wire), cable color: RAL 7000 (gray), secured using 4-40 UNC thread, IP20 protection, head 1 with socket shell 1 and straight cable outlet, head 2 with pin shell 1 and straight cable outlet, length: 5 m

RoHS

Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 029735
GTIN	4046356029735

Technical data

Mechanical characteristics

Number of positions	9
Insertion/withdrawal cycles	≥ 50
Cable outlet	straight
Length of cable	5 m
Degree of protection	IP20

Ambient conditions

Ambient temperature (operation)	0 °C ... 70 °C
Degree of protection	IP20

Material data

Housing material	PVC
Contact material	Copper alloy
Contact surface material	gold-plated
Outer sheath, material	PVC

Electrical characteristics

Number of positions	9
Rated current	1 A

D-SUB cable - VS-09-DSUB-20-LI-5,0 - 1656259

Technical data

Electrical characteristics


Overvoltage category	III
Degree of pollution	2
Rated voltage (III/3)	125 V

Environmental Product Compliance


China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings


Dimensional drawing




Dimensional drawing




Circuit diagram



Schematic diagram



Schematic diagram



Approvals

Approvals

D-SUB cable - VS-09-DSUB-20-LI-5,0 - 1656259

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		B.00767
-----	---	---------

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>