

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130105-0035](#)
Status: **Active**
Description: Watertite® Wet Location 35W 12V Flood Light with In-line Transformer, Screw Release Guard, 14/2 SOOW, Overall Length 7.62m (50.0')

Documents:
[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130105](#)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet None
Product Literature Order No 987650-8052
Product Name Watertite®
Type Specialty Light
UPC 78678861532
Woodhead Yes

Physical

Cord Length - Primary 3.04m (10.0')
Cord Length - Secondary 15.24m (50.0')
Depth N/A
Duty Wet Location
Guard Included No
Guard Type N/A
Height 127.00mm (5.000")
Length 228.60mm (9.000")
Material - Guard #10 Gauge Vinyl Coated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Quartz Halogen
Cord Type - Primary 16/3 SOOW
Cord Type - Secondary 14/2 SOOW
Lamp Type PAR36
Lamp Wattage - Maximum 35W
Lumens 350
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Old Part Number 1612



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130105Series](#)