

Search Results

- Evaluate
 - FAQ's
- How to Buy
 - Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) [Search Tips](#)

Text Search: 'F9PE10P-NM8'

Your search criteria matched only one product, shown below

F9PE10P-NM8



- Pass all TIA/EIA-568-B.3 performance requirements
- 100% factory inspected end face geometry in compliance with Telcordia GR-326-CORE, Issue 3
- Typical insertion loss per connection: 0.25dB
- UPC polished (55dB minimum return loss)
- Include color-specific keys with positive and negative keying features to visually and mechanically distinguish connections to prevent unauthorized mating with unlike keyed or non-keyed adapters
- Part of a complete keyed LC system that includes Opti-Core® Patch Cords and Pigtails, OptiCam® Pre-Polished Cam Connectors, Opticom® Fiber Adapter Panels (FAPs) and Mini-Com® Adapter Modules
- Factory terminated and 100% tested for insertion loss and return loss
- Insertion loss and return loss data recorded for every singlemode patch cord
- Lifetime traceability of test data to a Q.C. number on each patch cord
- Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.

Additional keyed colors include the following: G–Violet, H–Aqua, J–Rose, K–Slate, L–Brown, P–White, Q–Charcoal, R–Lavender, S–Peach, T–Steel Blue, V–Maroon and W–Mint.

| | |
|--------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------|
| ▪ Part Number | F9PE10P-NM8 |
| ▪ RoHS Compliance Status | Compliant |
| ▪ Note | Intended for use in fixed installations which are outside the scope of RoHS. |
| ▪ Part Description | LC (keyed P – White) to pigtail singlemode duplex pigtail, 1.6mm jacketed cable (one duplex keyed LC connector on one end and open on the other end) – 9/125µm. |
| ▪ Product Type | Keyed LC Patch Cords |
| ▪ Length (m) | 8 |
| ▪ Fiber Compatibility | 9/125µm |
| ▪ Fiber Cable Size | 1.6mm |
| ▪ Fiber Cable Type | Jacketed |
| ▪ Fiber Type | Singlemode |
| ▪ Connector 1 Type | LC Connector - Keyed P - White |
| ▪ Connector 2 Type | Pigtail |
| ▪ Flammability Rating | Plenum (OFNP) |
| ▪ Key Type and Color | Keyed P-White |
| ▪ Pricing Description | LC (keyed P - White) to pigtail 9/125µm singlemode, duplex patch cord, 1.6mm jacketed cable, 8M |
| ▪ Min. Order UOM | PC |
| ▪ Min. Order Qty. | 1 |
| ▪ BOM Qty. (# of Pkgs.) | <input type="text" value="0"/> |
| ▪ Add to Favorite Product List | <input type="checkbox"/> |

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.