



HONEYWELL PART NUMBER
-

REV	DOCUMENT	CHANGED BY	CHECK
3	0041144	SS 26JUN08	BLR



CORROSION RESISTANT
STEEL ACTUATOR



RELEASE NO. PR21569	CATALOG LISTING CW-B1734
REPLACES -	

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:		DRAWN	DCS	16FEB95	Honeywell					
OPERATING FORCE ---- 46 GRAMS MAX		CONTACT ARRANGEMENT S P N O				CHECK	-	-						
RELEASE FORCE ----- 4 GRAMS MIN		L215 15.1A 1/2HP 125, <u>250</u> OR 277 VAC 1/2A 125 VDC 1/4A 250 VDC; 5A 125 VAC "L" 		NO PLACES X ± -		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH, BASIC					
DIFFERENTIAL TRAVEL ----- .054 MAX				ONE PLACE .X ± 0.030										
OVERTRAVEL ----- .124 MIN				TWO PLACE .XX ± 0.015		INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY								
RELEASE TRAVEL ----- .030 MIN				THREE PLACE .XXX ± 0.005										
				ANGLES X ± -					SIZE	TYPE	CAGE CODE	DRAWING NAME		REV
				THIRD ANGLE PROJECTION 					B	I	-	V7-1C27D8-048-1		3
						Pro/ENGINEER 2D			SCALE	-			SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-1C27D8-048-1](#)