

TABLE I					
DASH	A INSIDE DIA			B OUTSIDE DIA	
	NO	MIN	MAX	MIN	MAX
09	.24	(6.1)	.28 (7.1)	.38 (9.7)	.42 (10.7)
12	.33	(8.4)	.37 (9.4)	.48 (12.2)	.52 (13.2)
14	.40	(10.2)	.44 (11.2)	.55 (13.9)	.59 (15.0)
16	.45	(11.4)	.50 (12.7)	.60 (15.2)	.66 (16.8)
20	.57	(14.5)	.62 (15.7)	.71 (18.0)	.77 (19.5)
24	.69	(17.5)	.75 (19.1)	.88 (22.4)	.94 (23.9)
28	.81	(20.6)	.87 (22.1)	1.00 (25.4)	1.08 (27.4)
32	.93	(23.6)	1.00 (25.4)	1.12 (28.4)	1.20 (30.5)
36	1.07	(27.2)	1.13 (28.7)	1.25 (31.8)	1.33 (33.8)
40	1.19	(30.2)	1.25 (31.8)	1.37 (34.8)	1.45 (36.8)
44	1.32	(33.5)	1.38 (35.0)	1.50 (38.1)	1.58 (40.1)
48	1.45	(36.8)	1.50 (38.1)	1.63 (41.4)	1.71 (43.4)
52	1.58	(40.1)	1.63 (41.4)	1.76 (44.7)	1.84 (46.7)
56	1.70	(43.2)	1.75 (44.5)	1.88 (47.8)	1.96 (49.8)

PART NUMBER DEVELOPMENT

EXAMPLE: 120 - 126 - 16 R

PRODUCT SERIES

BASIC NO-

DASH NO, TABLE I-

COLOR OPTION


BL = BLUE

R = RED

Y = YELLOW

TN = DESERT TAN

(OMIT FOR STD. BLACK)



NOTES:

1. IDENTIFY WITH MANUFACTURERS NAME AND P/N.
2. METRIC DIMENSIONS (IN PARENTHESES) ARE GIVEN FOR REFERENCE ONLY, AND ARE BASED UPON 1 INCH = 25.4 mm.
3. UNLESS OTHERWISE SPECIFIED, CONDUIT WILL BE SHIPPED PER STANDARD PACKAGE MIN LENGTH SUPPLIED WILL BE 10 FEET (3m) WITH A MAX OF 4 LENGTHS PER PKG
4. CONSULT FACTORY FOR AVAILABILITY OF INDICATED SIZE.

5. MATERIAL/FINISH:

CONVOLUTED TUBING - KYNAR

SYNOPSIS		REVISIONS	
SYN.	DESCRIPTION	DATE	APPROVED
A	RELEASED	08/20/02	MP
B	REVISED PER DCN #20075	11/12/02	DM.
C	REVISED PER DCN #20210	12/17/02	KB
D	REVISED PER DCN #20725	04/22/03	DM.
E	REVISED PER DCN #36954	10/15/10	ACM
F	REVISED PER DCN #47957	09/23/13	ACM

STANDARD SHIPPING PACKAGE 3	
DASH NO	MAX LENGTH PER PKG
09 & 12	200 FT (60 m)
16 THRU 52	100 FT (30 m)

THIS COPIRIGHTED DOCUMENT IS THE PROPERTY OF GLENLAIR, INC. AND IS FURNISHED ON THE CONDITION THAT IT IS NOT TO BE DISCHARGED, REPRODUCED IN WHOLE OR IN PART, OR USED TO SOLICIT QUOTATIONS FROM, COMPETITIVE SOURCES OR USED FOR MANUFACTURE BY ANYONE OTHER THAN GLENLAIR, INC. WITHOUT WRITTEN PERMISSION FROM GLENLAIR, INC. THE INFORMATION HEREIN HAS BEEN DEVELOPED AT GLENLAIR'S EXPENSE AND MAY BE USED FOR ENGINEERING EVALUATION AND INCORPORATION INTO TECHNICAL SPECIFICATIONS AND OTHER DOCUMENTS WHICH SPECIFY PROCUREMENT OF PRODUCTS FROM GLENLAIR, INC.									
UNLESS OTHERWISE SPECIFIED			DRAWN MP		08/20/02		GLENLAIR, INC. 1211 AIR WAY - GLENDALE - CALIFORNIA 91201 CAD 1987		
DIMENSIONS ARE IN INCHES			CHECK MP	08/20/02		TUBING, CONVOLUTED, ANNULAR, SPLIT			
			ENGR MP	08/20/02					
FRACTIONS ± 1/16 DECIMALS .XX .03 ANGLES ± 2°			 APPROVED						
RELEASE DATE			08/27/02			CODE IDENT. NO.		SIZE	
ORIGINAL RELEASE DATE			08/27/02			06324		C 120-126	
DO NOT SCALE THIS DRAWING						REV.		F	
B/O	02-1837	P/C 12	NON REPARABLE COMMERCIAL ITEM			SCALE N/A		WEIGHT N/A	
								SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Glenair:

[120-126-24BL](#) [120-126-48BL](#) [120-126-16](#) [120-126-16R](#) [120-126-40](#) [120-126-16BL](#) [120-126-14BL](#) [120-126-09](#)
[120-126-12](#) [120-126-20BL](#) [120-126-48](#) [120-126-20](#) [120-126-14](#) [120-126-20R](#) [120-126-32BL](#) [120-126-40BL](#) [120-](#)
[126-09BL](#) [120-126-32](#) [120-126-52](#) [120-126-24](#) [120-126-28](#) [120-126-52BL](#) [120-126-12BL](#) [120-126-16Y](#) [120-126-](#)
[28BL](#)