

Catalog Number: TYS24-470C
Product ID: 7TAG009460R0120
UPC Number: 78621091542
EAN Number: 05414363067931
Status: A



Multi-Lok 316 Stainless Steel Cable Tie, Black Nylon 11 Coated for High Temperature Applications, Weather and Ultraviolet Resistant, Length of 610mm (24 Inches), Width of 12mm (0.47 Inch), Thickness of 0.4mm (0.02 Inch), Tensile Strength Rating of 1112 Newtons (250 Pounds)

- Application Tools: WTAE200, WTAE201,

Actual



Actual

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5046 Stainless Steel Ties
Brand Name	Ty-Rap
Type	Multi-Lok Self-Locking
Standard	UL E49405
Width	0.47 in ; 12 mm
Length	24 in ; 610 mm
Thickness	0.02 in ; 0.4 mm
Bundle Diameter	Max 9.1 in ; Max 230 mm
Material	316 Stainless Steel
Color	Black
Lock Mechanism	Multi-Lok
Tensile Strength	250 pounds ; 1112 newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	12mm
Length belt/tape/tie	610mm
Tie thickness	0.4mm
Max. bundle diameter	230mm
Min. holding force	1112N
Operating temperature	-40-+150°C
Model	Internal toothing
Band closure	Ball latch
Material	Metal
Material quality	Stainless steel 316 (V4A)
Surface protection	Plastic-coated
Halogen free	Y
Colour	Beige
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

Packaging

Inner Quantity	100
Outer Quantity	1000
Outer Dimensions (inches)	12x7x5
Weight Uom	3.2 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	TDS000433
--------------------------------	-----------

Technical Drawing / Data Sheet Canada Available on Website

For further technical assistance, please contact us...

ABB Installation Products - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

ABB Installation Products Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com