


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES, UNLESS OTHERWISE SPECIFIED:

FULLY AUTOMATIC PUMP SPECIFICATIONS

MOTOR:


Type: Commutator
RPM: 1200
Voltage: AC 120V
Frequency: 50/60 Hz
Current: 6.5A
Horsepower: 1/2

PUMP:

Low Pressure: 20kg/cm² (300 psi)
Delivery: 2.6 Liters/Min.
High Pressure: 600 Kg/cm² (10,000 psi)
Delivery: .32 Liters/Min.
Oil Tank Cap.: 2 Liters
Weight: 15 kg (33 lbs.)
Fluid Type: Shell Tellus S2V15 Hydraulic Oil
Housing Color: Orange

SEE SHEET 2 FOR FEATURES

F:\wrkgrp\rvusers\ENGR DOCS\CUST DWGS\TP24507A01 02 CT-901HP CD.doc

							CT-901HP HYDRAULIC PUMP					
							CUSTOMER DRAWING					
							ITEM REVISION NAME:					
							TP24507A01_02					
---	-----	----	----	----	UPD PHOTO, UPD BRANDING AND DWG.	----	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:			MATERIAL:		
02	5-23-13	BLR			TEMPLATE; CHNG TO SHELL TELLUS S2V15 OIL	4609	(.x) ± --- (.xxx) ± --- (.xx) ± --- ANGLES ± ---			NONE		
01	8-03-07	BLR	BJPU	ABJ	REDRAWN	4255	 THIRD ANGLE PROJECTION			DRAWING NUMBER: TP24507A01		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY: BLR	DATE: 8-03-07	CHK BJPU	SCALE NONE	SHT 1 OF 2	SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTE: Used with separate crimping head, hydraulic pump and hose


- Crimps with CT-930CH, CT-940CH, and CT-980CH remote crimping heads:
 - CT-930CH – Accepts up to 750MCM Copper (600MCM Aluminum) lugs (400MCM Copper and Aluminum splices). Also specific C-Taps and H-Taps.
 - CT-940CH – Accepts up to 1500MCM Copper (1000MCM Aluminum) lugs and splices. Also specific C-Taps and H-Taps.
 - CT-980CH – Accepts 4 AWG to 750MCM Copper and Aluminum lugs and splices.
- CT-900HPH pre-filled hydraulic 10 foot hose

FEATURES:

- Manual Control
- Remote pump control
- Pressure adjustment 300 to 10,000 psi
- Visual fluid level
- External air vent and filler port
- Heavy gauge steel protective cover
- Two stage pumping action
- Automatic bypass when predetermined pressure is reached – pump shuts off automatically
- Built-in electrical solenoid switch to allow quick release of any cutter or crimper
- Small, compact, portable unit with carrying handle – standard 3/8" connection

SEE SHEET 1 FOR TOOL SPECIFICATIONS

F:\wrkgrp\rvusers\ENGR DOCS\CUST DWGS\TP24507A01_02 CT-901HP CD.doc

							CT-901HP HYDRAULIC PUMP					
							CUSTOMER DRAWING					
							ITEM REVISION NAME:					
							TP24507A01_02					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL:			
							(.x) ± --- (.xxx) ± --- (.xx) ± --- ANGLES ± ---		NONE			
							 THIRD ANGLE PROJECTION		DRAWING NUMBER:			
02	5-22-13	----	----	----	SEE SHEET 1		----		TP24507A01			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY: BLR	DATE: 8-03-07	CHK BJPU	SCALE NONE	SHT 2 OF 2	SIZE A